

FEWM24



Article Number: 855-04208

Wall Mount Fiber Enclosure - Unloaded, accepts 4 Adapter Panels, 2 Splice Trays, Black, 1/pkg

 Download spec sheet

Base Data

Local Order Number	FEWM24
Type	FEWM24
Color	Black (BK)
Features and Benefits	<ul style="list-style-type: none"><li>• Durable stainless steel construction for long life.</li><li>• Cable management spools for effective slack management.</li><li>• Bend radius control to minimize hand and wrist strain.</li><li>• Smooth grommet entry to protect cables from damage.</li><li>• Locking tab for added security.</li><li>• Meet ANSI/TIA/EIA 568-B standards.</li></ul>
Product Description	To effectively manage optical fiber terminations and splices, HellemannTyton offers a line of wall mount enclosures. They provide a termination solution for LAN applications requiring fully enclosed wall mount enclosures. This product is designed to support up to four modular adapter panels, providing the flexibility to have up to 36 fibers when fully loaded. This enclosure houses two splice trays.
Technical Description	HellermannTyton wall mount fiber enclosures provide a secure termination solution for LAN applications requiring fully enclosed and/or lockable enclosures. Wall mount enclosures accommodate up to 144 fibers, mount easily and provide easy cable routing access behind the enclosure. Choose from enclosure options to accommodate 1, 2 or 4 standard LGX-style adapter panels.
Short Description	Wall Mount Fiber Enclosure - Unloaded, accepts 4 Adapter Panels, 2 Splice Trays, Black, 1/pkg

Product Dimensions

Length L (Imperial)	3.5 "
Length L (Metric)	88.9 mm
Width W (Imperial)	15.0 "
Width W (Metric)	381.0 mm
Height H (Imperial)	15.63 "
Height H (Metric)	397.0 mm
Depth D (imperial)	3.7 "
Depth D (metric)	93.98 mm

Logistics and Packaging

Quantity Per	box
Package Quantity	1
Package Quantity (Metric)	1
Carton Quantity	1

Material and Specifications

**Material** Metal

**Material Shortcut** Metal

---

© HellemannTyton 2015