

Cover profile - FBP-3/10 TR - 3069924

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover profile, can optionally be sealed, Length: 114 mm, Width: 74.1 mm, Height: 32 mm, Color: transparent

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 137414
GTIN	4055626137414
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	39162000
Country of origin	Poland

Technical data

General

Color	transparent
Insulating material	PVC
Flammability rating according to UL 94	V0
Overvoltage category	III
Insulating material group	I
Ambient temperature (operation)	-15 °C ... 65 °C

Dimensions

Width	74.1 mm
Length	114 mm
Height	32 mm

Cover profile - FBP-3/10 TR - 3069924

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000886
ETIM 5.0	EC002848
ETIM 6.0	EC002848

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121410