

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732511853

Status:

Active

Overview:

Precision Compression-Mount Microwave Test Connectors

Description:

50 Ohms, Precision Test Connector, Optimized SMA Jack, Two Hole Flange with 2 Screws 6.35mm, 0-80 Threads



Documents:

HFSS Model

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	RF/Coax Connectors
Series	73251
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Style	PCB
Type	Subminiature
UPC	883906210809
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	1.820/g
Orientation	Straight
PCB Mounting	Surface Mount
PCB Thickness - Recommended	4.70mm
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Flange
Reverse Polar	No
Electrical	
Frequency	27 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73251-185-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73251 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION