

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732055033

Status:

Active

Overview:

TNC RF Connectors

Description:

50 Ohms, TNC Right-Angle PCB Bulkhead Jack Receptacle

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	RF/Coax Connectors
Series	73205
Overview	TNC RF Connectors
Product Name	TNC
Style	PCB
Type	Miniature
UPC	800753691582
Wire/Cable Type	N/A
Physical	
Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	22.776/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
Electrical	
Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73205-5033



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73205 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION