

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732513480

Status:

Active

Overview:

Precision Compression-Mount Microwave Test Connectors

Description:

50 Ohms, Precision Test Connector, Optimized SMA Jack, Flange with 0-80 Threads, 27 GHz, Without Screws



Documents:	
3D Model (PDF)	HFSS Model
3D Model	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

General	
Product Family	RF/Coax Connectors
Series	73251
Comments	27 GHz
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Type	Subminiature
UPC	883906534073
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	1.499/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No
Electrical	
Frequency	27 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73251-348-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[73251](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION