

CAN 2 METER CABLE WITH CAN BUS TERMINATORS

☆☆☆☆☆ [Write a review](#)

SKU: GC-CAN-CAB-2MT-GC

MPN:



-

1

+

[ADD TO CART](#)

SHARE:

**DELIVERY:** USUALLY
SHIPS THE SAME
BUSINESS DAY**AVAILABILITY:** IN
STOCK**30 DAY MONEY BACK
GUARANTEE *SOME
EXCEPTIONS APPLY****WARRANTY:** 1 YEAR
COMPREHENSIVE
SUPPORT FOR ALL
PRODUCTS

DESCRIPTION

REVIEWS

Q&A

This CAN Cable (compare to Peak PCAN Cable 2 IPEK-003001) is 2 meters in length with DB9 female connectors on each end WITH 120 ohm terminators in each DB9. The cable is 100 Ohm stranded 24 AWG copper paired conductors; electronic grade flexible polyethylene insulation, tinned copper shield and a flame retardant violet PVC jacket. The cable meets UL-Type CMX and CSA-Type CMX specs. The DB9 Connectors conform to CiA DS102-1.

A terminator should be used at the end of each bus system, the terminator provide line balancing for best CAN signals.

Call or email us for pricing on custom lengths.

For use with all versions of these Peak PCAN adapters:

- USB
- PCI
- mini PCI
- Compact PCI
- Express
- PCMCIA
- PC/104
- PC/104+

SUPPORT

We have the best technical support engineers that know how to use our products. If our Tech Support cannot solve your problem, we will contact the design engineer or manufacturer to help find a resolution.

 **CONTACT US**



PRODUCTS

WHY US?

RETURNS

CUSTOM/OEM PRODUCT ENGINEERING

BLOG

SHIPPING

SUPPORT

CERTIFICATIONS

ORDERING

CONTACT US

REQUEST A QUOTE

PRIVACY POLICY

TERMS & CONDITIONS

GET OUR NEWS FIRST

SUBMIT

