

ODLC-65-1050DA

AC-DC Constant Current mode (CC) LED driver with PFC; Input range 180-295VAC; Output 62VDC at 1.05A; Dimming with DALI

[Print preview](#)

Quantity: piece(s)

Multiple order quantity: 24

Minimum order quantity: 1

Price

[Add to basket](#)

[Add to wish list](#)
[Add to quote list](#)
[+ Compare](#)



[+ Hover and scroll to zoom](#) | [Click to enlarge](#)



[Specifications](#) | [Certification](#) | [Manual](#)

Specifications

Technical data		Information	
Brand	Mean Well	RoHS	Compliant
Item number	ODLC-65-1050DA	Packing quantity	24
Description	AC-DC Constant Current mode (CC) LED driver with PFC; Input range 180-295VAC; Output 62VDC at 1.05A; Dimming with DALI	Net weight (gram)	430
Format	Box Type - Enclosed		
Application	LED EN 61347		
Output Power (W)	65		
Output Voltage (V)	62		
Output Current (A)	1.05		
Input Voltage (V)	180-295V		
IP Rating	IP20 IP30 IP40 IP42 IP64 IP65 IP66 IP67		
Format	Box Type - Enclosed		
Width	77		
Height	28.5		
Depth	121		
Dimming Technology	DALI		

Certification

 [CB Certificate](#)

 [EMC Certificate](#)

 [UL Certificate](#)

Manual

 [Manual](#)



Quicklinks

Home	Login	Wishlist
RMA & Customer service	My account	Basket
About Mean Well Web	Power Supplies	Industries & Markets
	New Products	Contact us

Addresses

Office in the Netherlands
Minervum 7139
4817 ZN BREDA

+31 76 578 20 00
info@telereurope.com

Office in Belgium
Bisschoppenhoflaan 255
2100 ANTWERPEN

+32 3 326 40 00
info@telereurope.com