


MATERIAL BODY: BRASS PER ASTM B 16
 M CONTACT: BRASS PER ASTM B 16
 F CONTACT: BERYLLIUM COPPER PER ASTM B 196
 INSULATOR: PTFE FLUOROCARBON, ASTM-D1710
 FINISH: BODY: PROPRIETARY BRIGHT NICKEL (IP23)
 CONTACTS: GOLD PLATE PER MIL-G-45204

IMPEDANCE: N/A
 FREQUENCY RANGE: N/A
 VOLTAGE RATING: 350 VRMS
 INSULATION RESISTANCE: 5000 MEGOHMS
 FORCE TO ENGAGE/DISENGAGE
 LONGITUDINAL: 5 LB'S MAX
 TORQUE: 3 1/2 IN-LB'S



COVER DRAWING

APPROVED		DRAWN BY		TITLE	
D GOULD	11-3-95	B THOMMEN	11-3-95	BNC QUADRAX JACK	
A		SCALE		RECEPTACLE	
A1		1:3		CAD FILE: 7559	
D GOULD 11-29-95 REMOVE MTG HARDWARE UPDATE DIMS		DATE		PART NO.	
		11-3-95		21JR123-1	
		SHEET		OF	
		1		1	
FSCM NO. 24931					