



Ergonomic Full Cycle Ratchet
Hand Crimper, #12 AWG - #2 AWG
Copper Stranded, Solid and Flex
Wire, For use with Copper
Terminals, Splices and C-Taps

By Burndy
Catalog # [Y122CMR](#)



Ergonomic Full Cycle Ratchet Hand Crimper, #12 AWG - #2 AWG Copper.

Features

- Overmolded comfort grip handles
- Easy groove identification with color coded dies
- UL Listed/CSA Certified connections when used with recommended BURNDY terminals/splices
- Die index embossment for all 6 wire ranges
- Emergency release mechanism in case of misalignment or mistaken die choice
- Two different kits are also available with a selection of connectors in a sturdy metal carrying case (Y122CMRKIT and Y122CMRCIKIT)

Application

Crimping

General

Application - For Use On	#12-2 AWG Copper Terminals and Splices and #14-4 AWG Thin-Wall C-Taps
Die Type	Rotating Die Wheel
EU RoHS Indicator	No
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810659694
UPC 12 Digit	7818106596944

Dimensions

Dimensions	10.38 in x 0.75 in x 3.00 in
Height	3 in
Length	10.38 in
Weight	1.3 lb
Width	0.75 in

Conductor Related

Crimping Ranges	Copper: #12 AWG - #2 AWG Stranded, Solid and Flex
-----------------	---

Certifications And Compliance

Standards - RoHS Compliance UI
Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - BUR_50030110_SOMI_Y122CMR](#)
[Sales Drawings - 50030115](#)
[Video - Y122CMR Ratcheting Full Cycle Crimper](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-Y122CMR-SPEC-EN | REV 5/2024