



- Position setting of truck rear-view mirror
- Front panel adjusting knob

- Compact dimensions
- Design flexibility
- 5 Mio. cycles
- Very good resolution, better 0,1°

- Custom shafts design
- Electrical angles between 20° and 300°
- Mechanical angles between 45° and 316°

Mechanical Data		
Mechanical range	316	°
Torque	max. 0.5	Ncm
Min. life (mechanical)	5 Mio.	cycles
Operating temperature	-25 ... +85	°C
Storage temperature	-55 ... +105	°C
Protection class	IP65	

Insulating resistance (500 VDC, 1bar, 2s)	10	GOhm
Dielectric strenght (VAC, 50Hz, 1min, 1bar)	750	V
Vibration (Amax = 0.75mm, f = 30 ... 2000 Hz)	10	g
Shock (half sine pulse, 7 ms)	50	g

Contelec AG
Portstrasse 38
CH-2503 Biel/Bienne
Phone +41 (0)32 3665600
Telefax +41 (0)32 3665604
sales@contelec.ch

CONTELEC