



# leopard imaging inc

HOME

COMPANY

PRODUCT

ODM SERVICES

CONTACT

DISTRIBUTORS

ONLINE STORE

## PRODUCT

- ▶ Box HD IP Camera
  - 1080p IP Camera
    - 30fps
    - 60fps
  - 720p IP Camera
  - WDR IP Camera
    - 1080p - 30fps
    - 1080p - 60fps
    - 720p
  - Dual Camera
- ▶ OEM HD IP Camera Module
  - 1080p IP Camera
  - 720p IP Camera
  - WDR IP Camera
    - 1080p
    - 720p
- ▶ Dome HD IP Camera
  - 1080p IP Camera
  - 720p IP Camera
  - WDR IP Camera
    - 1080p
    - 720p
- ▶ CMOS Camera Board
  - Sony
  - Panasonic
  - Aptina
  - Omnivision
  - AltaSens
- ▶ USB Camera
- ▶ H2NVR
- ▶ Thermal IP Camera
- ▶ CMOS Sensor Module
  - Module
  - Demo Board
- ▶ Development Kit
  - Leopardboard
  - DM36xEUCDK
  - DM36xECDK

## LNCQ111AR0331



BUY NOW



Overview

Specifications

Download

Model	LNCQ111AR0331
Image Input	
Sensor Type	Aptina 1/3" CMOS Sensor
Day/Night	Auto Switch (Optional Feature)
e-shoot	1/2 to 1/10,000
Enhance	Auto Enhance
Exposure	Auto Exposure
White Balance	Auto WB
Lens	Fix focus, IRIS support, C/CS mount lens support
Image Process	
Resolution	1920x1080, 1290x720, D1, SXVGA
Active Pixels	2048 (H) x 1536 (V)
Pixel Size	2.2 μm x 2.2 μm
Format	H.264, MPEG-4, JPEG
Frame Rate	H.264/MPEG-4: 30f/s
Network	
Protocols	TCP/IP, HTTP, FTP (client/server), SMTP, DHCP, DNS, NTP, RTP/RTCP
Protocol	ONVIF
Authentication	IEEE802.1X
Interfaces	
Network	10BASE-T/100BASE-TX (RJ-45)
Serial Port	RS-485 (PELCO-D Protocol)
Extension Storage	SD card x1
Alarm In/Out	One channel Input, one channel Output
Audio Input/Output	3.5 MM
Work Environment	
Weight	314 gram
Size	136mm*63mm*56mm
Power Supply	PoE (Optional) or DC12V
Power Consuming	<3w
Temperature	-10°C ~ 60°C
Humidity	10% ~ 80% no condense
Video Management Software	
OS	Microsoft Windows 98/2000/XP/Vista/Win7
Browser	Internet Explorer 6.0 or above
Record Software	Milestone xprotect (3rd software)

[About Us](#) | [Contact](#) | [Careers](#) | [Partners](#)  
[Content](#) [copyright](#) 2012 [Leopard Imaging Inc.](#) All rights reserved.

---