



YAV27LTC516FX

by Burndy
Catalog ID: YAV27LTC516FX

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 3/0 Flex, 5/16" Stud, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available.

Product Details

General

Application	For Flex Conductors
Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022498
UPC 12 Digit	7818100224988

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.21 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.36 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3/0 (450/#24) DLO
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - CopperWeld Str Size	3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)