


Products ▶ Systems ▶ 2U ▶ [6028R-E1CR12T]



Super X10DBH-CT

1. Dual socket R3 (LGA 2011) supports Intel® Xeon® processor E5-2600 v4[†] / v3 family; QPI up to 9.6GT/s
2. Up to **2TB[†]** ECC 3DS LRDIMM , up to DDR4- **2400[†]**MHz ; 16x DIMM slots
3. 1x PCI-E 3.0 x16, 6x PCI-E 3.0 x8
4. Dual 10GBase-T LAN w/ Intel® X540
5. 12x 3.5" Hot-swap SAS3/SATA3 drive bays; 2x 2.5" optional Hot-swap SATA drive bays (rear)
6. SAS3 (12Gbps) via LSI 3108 onboard HW RAID
7. Server remote management: IPMI 2.0 / KVM over LAN / Media over LAN
8. 3x 8cm hot-swap redundant PWM cooling fans
9. 920W Redundant Power Supplies **Platinum Level (94%)**

Note: Image above may show a varied configuration or optional parts. Please refer to parts list for standard parts included.

Specifications

Environmental Spec.

- Operating Temperature:
10°C to 35°C (50°F to 95°F)
- Non-operating Temperature:
-40°C to 70°C (-40°F to 158°F)
- Operating Relative Humidity:
8% to 90% (non-condensing)
- Non-operating Relative Humidity:
5% to 95% (non-condensing)

Parts List

[See Parts List](#)