



Modular Crimping Tool



Compression Crimping Tool



Crimping Tool



Stripper



Cutter & Stripper



Punch Down Tool



Cable Tie Fastening Tool



Fiber Optic Tool



Tool Kit & Cable Tester



Other

[Home](#) / [Product](#) / [Crimping Tool](#) / [Ratchet Crimping Tool](#) / [HT-336FM / HT-236FM \(Frame only\)](#)



HT-336FM
8.7"(220mm)













HT-236FM
8.7"(220mm)

ITEM NO.

OVERVIEW

PACKAGE

	Type no HT-	Die P/N	Specifications	Crimping cable size
	336A	3A	.256"/.068"/.213" 6.50/1.73/5.41mm	RG58, 59, 62
	336A4	3A4	.255"/.187"/.068"/.213" 6.48/4.75/1.73/5.41mm	RG58, 59, 62, 174
	336C	3C	.256"/.319"/.068"/.213" 6.50/8.10/1.73/5.41mm	RG58, 59, 62, 6
	336C1	3C1	.068"/.216"/.324"/.360" 1.73/5.49/8.23/9.14mm	RG58, 59, 62, 6
	336C2	3C2	.68"/.262"/.324"/.360" 1.73/6.65/8.23/9.14mm	CATV"F" Connectors RG59, 6
	336D	3D	.213"/.256"/.068"/.324" 5.41/6.50/1.73/8.23mm	RG58, 59, 62, 6
	336D1	3D1	.068"/.178"/.324" 1.73/4.52/8.23mm	RG58, 6, 174
	336D2	3D2	.256"/.429"/.068"/.213" 6.50/10.90/1.73/5.41mm	RG58, 59, 62, 11, 8, 213
	336D3	3D3	.390"/.275"/.065" 9.90/6.98/1.65mm	RG213, 6, 8, 59
	336F1	3F1	.042"/.068"/.133"/.162"/1.95" 1.07/1.73/3.38/4.11/4.95mm	Fiber Optic SMA(Oval Type)
	336F2	3F2	.042"/.068"/.151"/.178"/.213" 1.07/1.73/3.84/4.52/5.41mm	Fiber Optic SMA, SMB Conn. RG58, 174, Belden 8281

	336F3	3F3	.151"/.178"/.213" 3.84/4.52/5.41mm	RG58, 174, 179
	336F4	3F4	.151"/.178"/.134"/.139"/.190" 3.84/4.52/3.40/3.53/4.83mm	Fiber Optic ST, SC, LC connectors.
	336G	3G	.043"/.068"/.100"/.137"/.213"/.255" 1.09/1.73/2.54/3.48/5.41/6.48mm	RG58, 59, 62, 174 Fiber Optic
	336G1	3G1	.042"/.068"/.190"/.213" 1.07/1.73/4.83/5.41mm	RG58, Fiber Optic
	336G2	3G2	.235"/.128"/.065"/.042" 5.97/3.25/1.65/1.07mm	RG58, 174, 139, 185
	336G3	3G3	.042" / .068"/.255"/.324" 1.07/1.73/6.48/8.23mm	RG58, 59, 6
	336G4	3G4	.042"/.068"/.178"/.278"/.255" 1.07/1.73/4.52/7.06/6.48mm	RG59, 62, 174
	336H1	3H1	.255"/.320"/.350" 6.48/8.13/8.89mm	CATV F Connectors RG59, 6
	336H2	3H2	.320"/.210"/.185" 8.13/5.33/4.70mm	RG58, 6
	336I	3I	.254"/.211"/.093"/.067"/.315" 6.46/5.36/2.36/1.70/8.0mm	RG58, 59, 6, 174
	336J	3J	.042"/.068"/.078"/.128"/.151"/.178" 1.07/1.73/1.98/3.25/3.84/4.52mm	RG174, 179, Belden 8218 Fiber Optic
	336K	3K	.100"/.128"/.429" 2.54/3.25/10.90mm	RG8, 11, 174, 179,, 213 LMR400
	336K2	3K2	.068"/.256"/.429" 1.73/6.50/10.90mm	RG8, 11, 59, 62
	336K3	3K3	.256".068"/.295" 6.50/1.73/7.49mm	RG59, 6
	336K4	3K4	.100"/.128"/.190/.213" 2.54/3.25/4.83/5.41mm	RG58, 174, Fiber Optic
	336K5	3K5	.080"/.100"/.429" 2.03/2.54/10.90mm	RG11, 174, 213

	336K6	3K6	.429"/.075"/.075" 10.90/1.91/1.91mm	RG11, 213
	336M	3M	.288"/.268"/.305" 5.79/1.73/7.75mm	RG58, 59, 6, 62, 142
	336P1	3P1	.255"/.213"/.098"/.068"/.321" 6.48/5.41/2.49/ 1.73/8.15mm	RG58, 59, 62, 6
	336T1	3T1	.028"/.039"/.047"/.100"/.128"/.151" 0.71/0.99/1.19/2.54/3.25/3.84mm	RG174, 178, 179, 180, 187
	336V	3V	.043"/.069"/.100"/.128"/.151"/.213" 1.09/1.75/2.54/3.25/3.84/5.41mm	SMA, SMB, SMC, MCX
	336V1	3V1	.047"/.068"/.178"/.217"/.256"/.330" 1.19/1.73/4.52/5.51/6.50/8.38mm	RG59, 62, 6, 174, Fiber Optic
	336Y	3Y	.044"/.057"/.068"/.220"/.213" 1.12/1.45/1.73/5.59/5.41mm	RG58
	336Y1	3Y1	.218"/.069" 5.54/1.75mm	RG58(Oval Type)
	336Y2	3Y2	.042"/.240" 1.07/6.10mm	Pin terminal, insulated or non-insulated ferrules (Oval Type)
	236C	2C	AWG 20-18/16-14/12-10 DIN 0.5-1/1.5-2.5/4-6mm ²	Non-insulated terminal or open barrel terminal
	236C2	2C2	AWG 20-18/16-14 DIN 0.5-1/1.5-2.5mm ²	Non-insulated terminal or open barrel terminal
	236C3	2C3	AWG 24-30/18-22 DIN 0.25-0.05/1.0-0.5mm ²	D-Sub terminal
	236C4	2C4	AWG 24-28/20-22 DIN 0.25-0.08/0.75-0.5mm ²	D-Sub terminal
	236E	2E	AWG 22/20/18/16/14/12 DIN 0.5/0.75/1.0/1.5/2.5/4mm ²	Pin terminal insulated or non-insulated ferrules
	236E1	2E1	AWG 10/8/6 DIN 6/10/16 mm ²	Pin terminal insulated or non-insulated ferrules

--