




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECR-23-182036	07AUG2023	AK	JP







VIEW B-B



OBSOLETE	1.73 [44mm]	972366-5	1-1706504-2	147117-5	12	4-647166-2	1-1744382-2
	1.73 [44mm]	972366-5	1706504-8	147117-5	8	3-647166-8	1744382-8
	1.73 [44mm]	972366-5	1706504-7	147117-5	7	3-647166-7	1744382-7
	1.73 [44mm]	972366-5	1706504-6	147117-5	6	3-647166-6	1744382-6
	1.26 [32mm]	972366-4	1706504-5	147117-5	5	3-647166-5	1744382-5
	DIM A	COVER TAPE	CARRIER TAPE	PICK AND PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Ir_ruth CHK SAM MACE APVD SAM MACE PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019 WEIGHT —		30MAR11 30MAR11 30MAR11 NAME MTA100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, .025 SQ. POST, TAPE W/CAP SIZE A2		TE Connectivity DRAWING NO 00779 C-1744382 RESTRICTED TO —	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .015 4 PLC ± — ANGLES ± 1°		MATERIAL —		FINISH —	
CUSTOMER DRAWING				SCALE 3:1		SHEET 1 of 4	
				REV		B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



1.26 [32mm]	972366-4	1706504-4	147117-5	4	3-647166-4	1744382-4
DIM A	COVER TAPE	CARRIER TAPE	PICK AND PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN jr ruth 30MAR11	TE Connectivity	
DIMENSIONS: INCHES				CHK SAM MACE 30MAR11		
TOLERANCES, UNLESS OTHERWISE SPECIFIED:				APVD SAM MACE 30MAR11		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± 1°				PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019		
MATERIAL -				WEIGHT	SIZE A2	CAGE CODE 00779
FINISH -				CUSTOMER DRAWING	DRAWING NO C=1744382	RESTRICTED TO -
				SCALE 3:1	SHEET 2 of 4	REV B

D

C

B



A

D


C

B

A



MTA-100 HEADER SHOWN



OBSOLETE	4.200 [30.48mm]	12	4-647166-2	1-1744382-2
	.800 [20.32mm]	8	3-647166-8	1744382-8
	.700 [17.78mm]	7	3-647166-7	1744382-7
	.600 [15.24mm]	6	3-647166-6	1744382-6
	.500 [12.70mm]	5	3-647166-5	1744382-5
	.400 [10.16mm]	4	3-647166-4	1744382-4
	DIM L	NO. OF POSITIONS	HEADER ASSEMBLY	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .015
4 PLC ± -
ANGLES ± 1°
FINISH -

DWN jr ruth 30MAR11
CHK SAM MACE 30MAR11
APVD SAM MACE 30MAR11
PRODUCT SPEC 108-1050
APPLICATION SPEC 114-1019
WEIGHT
CUSTOMER DRAWING

TE Connectivity

MTA100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, .025 SQ. POST, TAPE W/CAP

SIZE A2 CAGE CODE 00779 DRAWING NO C=1744382 RESTRICTED TO -

SCALE 3:1 SHEET 3 OF 4 REV B

1744382

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A

A



1744382

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	jr ruth	30MAR11	TE Connectivity MTA100 HEADER ASSY, SURFACE MOUNT, FRICTION LOCK, .025 SQ. POST, TAPE W/CAP			
		CHK	SAM MACE	30MAR11				
		APVD	SAM MACE	30MAR11				
		PRODUCT SPEC	108-1050					
DIMENSIONS: INCHES [MM]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME			
		0 PLC	±	-	SIZECAGE CODEDRAWING NORESTRICTED TO			
		1 PLC	±	-				
		2 PLC	±	-				
		3 PLC	±	.015[0.40]				
MATERIAL-		4 PLC	±	-	A200779C=1744382			
		ANGLES	±	1°				
FINISH-		WEIGHT			CUSTOMER DRAWING			
					SCALE3:1SHEET4 OF 4REV B			