



YAV2CL2TC14FX90

by Burndy
Catalog ID: YAV2CL2TC14FX90

Prop 65 Notice

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, #2 Weld, 3(125/#24)-2(150/#24)DLO Flex, #2 AWG Code, 60 Navy, 600 V-35 kV, 1/4" Stud, 90 Deg Bent, Std bbl.

Two hole, copper compression terminal flex conductor, standard barrel

Product Details

General

Application	For Flex Conductors
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022221
UPC 12 Digit	7818100222211

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Height inch	1.15 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.60 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	11/16

Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3 (125/#24) DLO;2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)