

DIN EN 60603 (DIN 41612)

Type R




Male connector

Contact spacing

.100" and .200"

Press-fit Technology


**Directive 2002/95/EC
"RoHS"
Compliant**




Note:

Premating contacts available, please consult factory.


Press-fit tail length 4.6 mm



Wire Wrap 13 mm Sn



Wire Wrap 17 mm Sn/Au



Part Numbers

No. of Pos.	row	' = contact + = no contact Pos. 1 2 3 4 5 ...	Press-fit tail length 4.6 mm	Wire Wrap 13 mm Sn
64	a b c	• • • • • + + + + + • • • • •	121 A 21029 X	121 A 21059 X
96	a b c	• • • • • • • • • • • • • • •	121 A 21019 X	121 A 21069 X