

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
2.40"	ITLT0240QVCF25UM Integrated 4 Wire RTP	TTL	QVGA 240x320 3:4 Normally White, Transmissive	420	18 Bit	80/80/70/80	12 O'Clock	-20~70 -30~80	42.70 x 59.45 x 3.98 36.72 x 48.96
2.40"	ITLT0240QVCN23UM	TTL	QVGA 240x320 3:4 Normally White, Transmissive	500	18 Bit	80/80/70/80	12 O'Clock	-20~70 -30~80	42.70 x 59.45 x 3.00 36.72 x 48.96
3.50"	ITLT0350QVRF12CM Integrated 4 Wire RTP	TTL	QVGA 320x240 4:3 Normally White, Transmissive	250	24 Bit	60/60/50/55	6 O'Clock	-20~60 -30~70	76.90 x 63.90 x 3.26 90.08 x 52.56
3.50"	ITLT0350QVRT03CM Integrated 4 Wire RTP	TTL	QVGA 320x240 4:3 Normally White, Transmissive	250	24 Bit	60/60/50/55	6 O'Clock	-20~70 -30~80	76.90 x 63.90 x 3.26 90.08 x 52.56
3.50"	ITLT0350QVRN11CM	TTL	QVGA 320x240 4:3 Normally White, Transmissive	300	24 Bit	60/60/50/55	6 O'Clock	-20~70 -30~80	76.90 x 63.90 x 3.26 90.08 x 52.56
3.50"	ITLT0350QVRF22AM Integrated 4 Wire RTP	TTL	QVGA 320x240 4:3 Normally White, Transmissive	320	24 Bit	60/60/50/55	6 O'Clock	-20~70 -30~80	76.90 x 63.90 x 4.40 70.08 x 52.56
3.50"	ITLT0350QVRN20AM	TTL	QVGA 320x240 4:3 Normally White, Transmissive	320	24 Bit	60/60/50/55	6 O'Clock	-20~70 -30~80	76.90 x 63.90 x 3.30 70.08 x 52.56
4.30"	ITLT0430WQRF26CM Integrated 4 Wire RTP	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	400	24 Bit	70/70/50/70	12 O'Clock	-20~70 -30~80	105.50 x 67.20 x 4.05 95.04 x 53.86
4.30"	ITLT0430WQRF62WM Integrated 4 Wire RTP	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	400	24 Bit	75/75/55/75	6 O'Clock	-20~70 -30~80	105.40 x 67.10 x 3.90 95.04 x 53.85
4.30"	ITLT0430WQRP76ZM Integrated PCAP	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	400	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	105.50 x 67.20 x 4.65 95.04 x 53.86
4.30"	ITLT0430WQRN25CH	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	500	24 Bit	70/70/50/70	12 O'Clock	-20~70 -30~80	105.50 x 67.20 x 2.90 95.04 x 53.86
4.30"	ITLT0430WQRF64ZH Integrated 4 Wire RTP	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	700	24 Bit	75/75/55/75	6 O'Clock	-20~70 -30~80	105.40 x 67.10 x 3.90 95.04 x 53.85
4.30"	ITLT0430WQRN63ZH	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	800	24 Bit	75/75/55/75	6 O'Clock	-20~70 -30~80	105.40 x 67.10 x 2.80 95.04 x 53.86
4.70"	ITLT0470WQRN31AM	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	440	24 Bit	50/55/65/65	6 O'Clock	-20~70 -30~80	114.24 x 72.88 x 3.15 103.68 x 58.75
5.00"	ITLT0500VGRF62ZL_A2 Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally White, Transmissive	200	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	117.65 x 88.43 x 10.22 101.60 x 76.18
5.00"	ITLT0500WVRF52WM Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	300	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	120.80 x 76.00 x 4.65 108.00 x 64.80

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
5.00"	ITLT0500WVRP55WM Integrated PCAP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	300	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	120.80 x 76.00 x 4.10 108.00 x 64.80
5.00"	ITLT0500WQRN34CM	TTL	WQVGA 480x272 16:9 Normally White, Transmissive	350	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	120.70 x 75.80 x 3.10 110.88 x 62.83
5.00"	ITLT0500WVRF54WH Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	700	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	120.80 x 76.90 x 6.43 108.00 x 64.80
5.00"	ITLT0500WVRN53WH	TTL	WVGA 800x480 16:9 Normally White, Transmissive	800	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	120.80 x 76.90 x 4.83 108.00 x 64.80
5.60"	ITLT0560VGRF23CM Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally White, Transmissive	160	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	126.50 x 100.00 x 7.25 112.90 x 84.67
5.60"	ITLT0560VGRF23CM_A1 Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally White, Transmissive	160	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	126.50 x 100.00 x 7.25 112.90 x 84.67
5.70"	ITLT0570VGRN31UM	TTL	VGA 640x480 4:3 Normally White, Transmissive	300	18 Bit	75/75/55/75	6 O'Clock	-20~70 -30~85	127.00 x 98.40 x 8.96 115.20 x 86.40
5.70"	ITLT0570QVRF33ZM Integrated 4 Wire RTP	TTL	QVGA 320x240 4:3 Normally White, Transmissive	400	18 Bit	80/80/70/80	12 O'Clock	-30~85 -30~85	144.00 x 104.60 x 13.80 115.20 x 86.40
5.70"	ITLT0570VGRF33UH Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally White, Transmissive	400	18 Bit	75/75/55/75	6 O'Clock	-20~70 -30~85	127.00 x 98.40 x 10.05 115.20 x 86.40
5.70"	ITLT0570QVRN31ZM	TTL	QVGA 320x240 4:3 Normally White, Transmissive	500	18 Bit	80/80/70/70	12 O'Clock	-30~85 -30~85	144.00 x 104.60 x 12.30 115.20 x 86.40
5.70"	ITLT0570VGRF23ZH_A3 Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally White, Transmissive	700	18 Bit	80/80/70/70	12 O'Clock	-30~85 -30~85	144.00 x 104.60 x 13.80 115.20 x 86.40
5.70"	ITLT0570VGRN21AH	TTL	VGA 640x480 4:3 Normally White, Transmissive	700	18 Bit	80/80/70/70	12 O'Clock	-30~85 -30~85	144.00 x 104.60 x 12.30 115.20 x 86.40
5.70"	ITLT0570VGRN33UH	TTL	VGA 640x480 4:3 Normally White, Transmissive	700	18 Bit	75/75/55/75	6 O'Clock	-20~70 -30~85	127.00 x 98.40 x 8.96 115.20 x 86.40
5.70"	ITLT0570QVRN34ZH_A1	TTL	QVGA 240x320 3:4 Normally White, Transmissive	1200	18 Bit	80/80/70/70	12 O'Clock	-30~85 -30~85	144.00 x 104.60 x 12.30 115.20 x 86.40
6.50"	ITLT0650WVLN16CM	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	400	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	155.20 x 89.40 x 8.50 143.40 x 76.70
6.50"	ITLT0650WVRN14CM	TTL	WVGA 800x480 16:9 Normally White, Transmissive	400	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	155.20 x 89.40 x 5.50 143.40 x 76.70

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
6.50"	ITLT0650VGLF14ZH Integrated 4 Wire RTP	LVDS	VGA 640x480 4:3 Normally White, Transmissive	640	24 Bit	80/80/70/70	6 O'Clock	-30~80 -30~80	153.00 x 118.00 x 12.40 132.50 x 99.40
6.50"	ITLT0650VGLN12AH	LVDS	VGA 640x480 4:3 Normally White, Transmissive	800	24 Bit	80/80/70/70	6 O'Clock	0~50 -20~60	153.00 x 118.00 x 10.90 132.50 x 99.40
7.00"	ITLT0700WVRF22ZL Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	200	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	164.90 x 100.00 x 7.25 154.08 x 85.92
7.00"	ITLT0700SWLN42CM	LVDS	WSVGA 1024x600 16:9 Normally White, Transmissive	250	24 Bit	75/75/70/75	6 O'Clock	-20~60 -30~70	165.75 x 105.39 x 3.40 153.60 x 90.00
7.00"	ITLT0700SWLP47CM_A3 Integrated PCAP	LVDS	WSVGA 1024x600 16:9 Normally White, Transmissive	250	24 Bit	85/85/85/85	6 O'Clock	-20~60 -30~70	184.00 x 121.00 x 4.90 153.60 x 90.00
7.00"	ITLT0700WVRN22CL	TTL	WVGA 800x480 16:9 Normally White, Transmissive	250	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	164.90 x 100.00 x 5.70 154.08 x 85.92
7.00"	ITLT0700SWLF43CL Integrated 4 Wire RTP	LVDS	WSVGA 1024x600 16:9 Normally White, Transmissive	280	24 Bit	75/75/70/75	6 O'Clock	-20~60 -30~70	165.70 x 105.40 x 4.92 153.60 x 90.00
7.00"	ITLT0700WVRF34CL Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	280	18 Bit	70/70/60/70	6 O'Clock	-20~70 -30~80	165.00 x 104.44 x 6.75 152.40 x 91.44
7.00"	ITLT0700WVRP37CM_A2 Advanced PCAP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	280	18 Bit	70/70/60/70	6 O'Clock	-20~60 -30~70	185.40 x 116.80 x 7.00 152.40 x 90.80
7.00"	ITLT0700WVRNB1CM	TTL	WVGA 800x480 16:9 Normally White, Transmissive	300	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	165.00 x 104.00 x 5.50
7.00"	ITLT0700WVRF16ZM Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	320	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90x 100.00 x 7.25 154.08 x 85.92
7.00"	ITLT0700WVRF24CM Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	320	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 7.25 154.08 x 85.92
7.00"	ITLP0700WXL64TM Integrated PCAP	LVDS	WXGA 1280x800 16:9 IPS Normally Black, Transmissive	350	24 Bit	89/89/89/89	Free IPS	-20~60 -30~70	161.00 x 107.00 x 5.35 149.76 x 93.6
7.00"	ITLT0700WVRN32CM_A2	TTL	WVGA 800x480 16:9 Normally White, Transmissive	350	18 Bit	70/70/60/70	6 O'Clock	-30~85 -30~85	165.00 x 104.44 x 5.20 152.40 x 91.44
7.00"	ITLT0700WVRP38CM_A3 Integrated PCAP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	350	18 Bit	70/70/60/70	6 O'Clock	-20~60 -30~70	185.40 x 116.80 x 7.00 152.40 x 90.80
7.00"	ITLT0700SVRF04ZM Integrated 4 Wire RTP	TTL	SVGA 800x600 4:3 Normally White, Transmissive	380	18 Bit	70/70/60/70	6 O'Clock	-20~70 -30~80	154.00 x 119.20 x 7.90 141.60 x 106.20

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
7.00"	ITLT0700WVLF26CM Integrated 4 Wire RTP	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	400	18 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 10.25 154.08 x 85.92
7.00"	ITLT0700WVLF34ZM Integrated 4 Wire RTP	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	400	18 Bit	70/70/60/70	6 O'Clock	-20~70 -30~80	165.00 x 104.44 x 6.73 152.40 x 91.44
7.00"	ITLT0700WVLN25CM	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	400	18 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 8.70 154.08 x 85.92
7.00"	ITLT0700WVRN24CM	TTL	WVGA 800x480 16:9 Normally White, Transmissive	400	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 5.70 154.08 x 85.92
7.00"	ITLT0700WVLNC2CM	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	500	24 Bit	70/70/60/60	6 O'Clock	-30~85 -40~95	165.00 x 104.00 x 9.53 152.40 x 91.44
7.00"	ITLT0700WVLF27ZH Integrated 4 Wire RTP	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	800	18 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 10.25 154.08 x 85.92
7.00"	ITLT0700WVRP38CH_A1 Integrated PCAP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	800	18 Bit	70/70/60/70	6 O'Clock	-20~70 -30~80	180.00 x 110.00 x 6.70 152.40 x 91.44
7.00"	ITLT0700WVLN27ZH	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	1000	18 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	164.90 x 100.00 x 8.70 154.08 x 85.92
7.00"	ITLT0700WVRN36CH	TTL	WVGA 800x480 16:9 Normally White, Transmissive	1000	18 Bit	70/70/60/70	6 O'Clock	-30~85 -30~85	165.00 x 104.44 x 5.20 152.40 x 91.44
7.00"	ITLT0700WVRT20WH Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	1000	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	164.90 x 100.00 x 7.25 154.08 x 85.92
8.00"	ITLT0800SVLN31ZM_A1	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	250	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~80	183.00 x 141.00 x 8.60 162.00 x 121.50
8.00"	ITLT0800SVRN21ZH	TTL	SVGA 800x600 4:3 Normally White, Transmissive	250	24 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	183.00 x 141.00 x 5.60 162.00 x 121.50
8.00"	ITLT0800WVRF62ZM Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	360	24 Bit	70/70/50/70	6 O'Clock	-30~85 -30~85	192.80 x 116.90 x 8.01 176.64 x 99.36
8.00"	ITLT0800SVRN22ZH	TTL	SVGA 800x600 4:3 Normally White, Transmissive	500	24 Bit	70/70/50/65	6 O'Clock	-20~70 -30~80	183.00 x 141.00 x 8.60 162.00 x 121.50
8.40"	ITLT0840SVLF46GM_A5 Integrated 4 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	350	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~85	189.75 x 149.40 x 9.55 170.40 x 127.80
8.40"	ITLT0840SVLV47ZM Integrated 5 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	350	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~85	189.75 x 149.40 x 10.20 170.40 x 127.80

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
8.40"	ITLT0840SVLN45GM_A3	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	400	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~85	189.75 x 149.40 x 8.00 170.40 x 127.80
8.40"	ITLT0840SVLF56GH Integrated 4 Wire RTP	TTL	SVGA 800x600 4:3 Normally White, Transmissive	800	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~85	189.75 x 149.40 x 9.55 170.40 x 127.80
8.40"	ITLT0840SVLN53TH	TTL	SVGA 800x600 4:3 Normally White, Transmissive	1000	18 Bit	75/75/60/70	6 O'Clock	-20~ 70 -30 ~ 80	203.00 x 142.50 x 5.70 170.40 x 127.80
8.40"	ITLT0840SVLV57GH Integrated 5 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	1000	18 Bit	75/75/60/70	6 O'Clock	-20~70 -30~80	203.00 x 142.50 x 8.05 170.40 x 127.80
9.00"	ITLT0900WVRN22HM	TTL	WVGA 800x480 16:9 Normally White, Transmissive	250	18 Bit	70/70/50/70	6 O'Clock	-20~70 -30~80	211.10 x 126.50 x 5.90 198.00 x 111.70
9.00"	ITLT0900WXLN42HM	LVDS	WXGA 1280x800 16:10 Normally White, Transmissive	250	24 Bit	70/70/70/50	6 O'Clock	-10~60 -20~70	206.76 x 135.06 x 3.60 193.90 x 121.20
9.70"	ITLP0970XGLF14CM_A1 Integrated 4 Wire RTP	LVDS	XGA 1024x768 4:3 IPS Normally Black, Transmissive	300	18 Bit	89/89/89/89	Free IPS	-20~70 -25~70	211.10 x 165.00 x 7.35 197.00 x 147.00
9.70"	ITLP0970XGLP17CM Integrated PCAP	LVDS	XGA 1024x768 4:3 IPS Normally Black, Transmissive	300	18 Bit	89/89/89/89	6 O'Clock	-25~70 -25~70	211.10 x 165.00 x 7.35 197.00 x 147.00
9.70"	ITLP0970XGLN13VM	LVDS	XGA 1024x768 4:3 IPS Normally Black, Transmissive	350	18 Bit	89/89/89/89	6 O'Clock	-20~70 -25~70	210.20 x 164.00 x 5.45 197.00 x 147.00
9.70"	ITLP0970XGLN12CM_A7	LVDS	XGA 1024x768 4:3 MVA Normally Black, Transmissive	420	18 Bit	89/89/89/89	Free MVA	-20~70 -25~70	210.20 x 164.00 x 5.45 197.00 x 147.00
9.70"	ITLP0970XGLP25CH Integrated PCAP	LVDS	XGA 1024x768 4:3 IPS Normally Black, Transmissive	510	18 Bit	89/89/89/89	Free IPS	-20~70 -25~70	236.70 x 183.60 x 6.15 196.61 x 147.45
10.10'	ITLT1010WXP47ZL Integrated PCAP	LVDS	WXGA 1280x800 16:9 Normally White, Transmissive	200	24 Bit	75/75/75/70	6 O'Clock	20~60 30~70	249.56 x 168.20 x 5.40 217.00 x 136.00
10.10'	ITLP1010WXL12CM Integrated 4 Wire RTP	LVDS	WXGA 1280x800 16:9 MVA Normally Black, Transmissive	350	24 Bit	85/85/85/85	Free MVA	-20~60 -30~70	229.46 x 149.10 x 4.25 216.96 x 135.60
10.10'	ITLP1010WXP15CM Integrated PCAP	LVDS	WXGA 1280x800 16:9 MVA Normally Black, Transmissive	420	24 Bit	85/85/85/85	Free IPS	-20~70 -30~80	257.00 x 157.00 x 5.40 216.96 x 135.60
10.10'	ITLT1010SWLN21VM	LVDS	WSVGA 1024x600 16:9 Normally White, Transmissive	500	18 Bit	80/80/70/80	6 O'Clock	-30~85 -30~85	244.00 x 143.00 x 12.40 222.70 x 125.28
10.20'	ITLT1020WVLF47ZM Integrated 4 Wire RTP	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	280	24 Bit	65/65/45/65	6 O'Clock	-30~85 -30~85	235.00 x 145.80 x 10.90 222.00 x 132.48



Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
10.20'	ITLT1020WVRF45ZM_A4 Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9	280	24 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	235.00 x 145.80 x 11.90 222.00x 132.48
10.20'	ITLT1020WVLN46ZM	LVDS	WVGA 800x480 16:9 Normally White, Transmissive	350	24 Bit	65/65/45/65	6 O'Clock	-30~85 -30~85	235.00 x 145.80 x 9.40 222.00 x 132.48
10.20'	ITLT1020SWLN21PM	LVDS	WSVGA 1024x600 16:9 Normally White, Transmissive	400	18 Bit	70/70/65/55	6 O'Clock	-20~70 -30~80	235.00 x 145.80 x 5.30 222.72 x 130.50
10.20'	ITLT1020WVRF43ZH Integrated 4 Wire RTP	TTL	WVGA 800x480 16:9 Normally White, Transmissive	800	18 Bit	65/65/45/65	6 O'Clock	-30~85 -30~85	235.00 x 145.80 x 11.9 222.00 x 132.48
10.40'	ITLT1040SVRF16ZL Integrated 4 Wire RTP	TTL	SVGA 800x600 4:3 Normally White, Transmissive	220	24 Bit	70/70/50/60	6 O'Clock	-20~70 -20~80	228.40 x 175.40x 7.45 211.20 x 158.40
10.40'	ITLT1040SVLN23ZL	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	250	18 Bit	75/75/50/60	6 O'Clock	-10~60 -20~70	228.40 x 175.40 x 10.80 211.20 x 158.40
10.40'	ITLT1040SVRN13ZL	TTL	SVGA 800x600 4:3 Normally White, Transmissive	250	24 Bit	70/70/50/60	6 O'Clock	-10~60 -20~70	228.40 x 175.40 x 5.90 211.20 x 158.40
10.40'	ITLT1040XGLF45TM_A2 Integrated 4 Wire RTP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	300	18 Bit	70/70/65/55	6 O'Clock	-20~70 -30~80	236.00 x 174.30 x 9.00 211.20 x 158.40
10.40'	ITLT1040SVLF33TM Integrated 4 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	320	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 7.20 211.20 x 158.40
10.40'	ITLT1040SVLV34TM Integrated 5 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	320	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 7.80 211.20 x 158.40
10.40'	ITLT1040XGLP47TM_A1 Integrated PCAP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	320	18 Bit	70/70/65/55	6 O'Clock	-20~70 -30~80	239.10 x 186.30 x 9.77 211.20 x 158.40
10.40'	ITLT1040SVLN26ZM	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	350	18 Bit	75/75/50/60	6 O'Clock	-10~60 -20~70	228.40 x 175.40 x 10.80 211.20 x 158.40
10.40'	ITLV1040XGLP46AM Integrated PCAP	LVDS	XGA 1024x768 4:3 MVA Normally Black, Transmissive	360	24 Bit	88/88/88/88	Free MVA	-30~80 -30~80	259.10 x206.30 x 9.40 210.40 x 157.80
10.40'	ITLV1040XGLV44AM Integrated 5 Wire RTP	LVDS	XGA 1024x768 4:3 MVA Normally Black, Transmissive	360	24 Bit	88/88/88/88	Free MVA	-30~80 -30~80	238.60 x 175.80 x 8.85 210.40 x 157.80
10.40'	ITLT1040SVLN31TM	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	400	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 5.60 211.20 x 158.40
10.40'	ITLT1040SVLN41AM	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	400	24 Bit	80/80/60/80	6 O'Clock	-30~85 -30~85	243.00 x 184.00 x 8.00 211.20 x 158.40

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
10.40'	ITLT1040VGRF24CM Integrated 4 Wire RTP	TTL	VGA 640x480 4:3 Normally Black, Transmissive	400	18 Bit	88/88/88/88	Free MVA	-30~80 -30~80	225.50 x 176.30 x 10.89 211.20 x 158.40
10.40'	ITLV1040XGLN42AM	LVDS	XGA 1024x768 4:3 MVA Normally Black, Transmissive	450	24 Bit	88/88/88/88	Free MVA	-30~80 -30~80	238.60 x 175.80 x 6.50 210.40 x 157.80
10.40'	ITLT1040VGRN22CM	TTL	VGA 640x480 4:3 Normally Black, Transmissive	500	18 Bit	88/88/88/88	Free MVA	-30~80 -30~80	225.50 x 176.30 x 7.81 211.20 x 158.40
10.40'	ITLV1040XGLN53TM	LVDS	XGA 1024x768 4:3 Normally Black, Transmissive	500	24 Bit	88/88/88/88	Free IPS	-30~70 -30~80	225.50 x 176.30 x 8.70 210.40 x 157.80
10.40'	ITLT1040SVRN15ZH	TTL	SVGA 800x600 4:3 Normally White, Transmissive	650	24 Bit	70/70/50/60	6 O'Clock	-10~60 -20~70	228.40 x 175.40 x 8.90 211.20 x 158.40
10.40'	ITLT1040SVLF37ZH Integrated 4 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	800	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 7.20 211.20 x 158.40
10.40'	ITLT1040SVLN32GH	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	1000	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 5.60 211.20 x 158.40
10.40'	ITLT1040SVLN35TM	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	1000	18 Bit	65/65/45/65	6 O'Clock	-20~70 -30~80	236.00 x 176.90 x 5.60 211.20 x 158.40
10.40'	ITLT1040VGLN24CH	LVDS	VGA 640x480 4:3 Normally White, Transmissive	1000	24 Bit	80/80/60/80	6 O'Clock	-30~ 85 -30~ 85	243.00 x 176.60 x 8.00 211.20 x 158.40
10.40'	ITLT1040XGLP48TH Integrated PCAP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	1000	18 Bit	70/70/65/55	6 O'Clock	-30~80 -30~80	259.10 x 206.30 x 10.10 211.20 x 158.40
12.10'	ITLT1210SVLP44ZL Integrated PCAP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	250	24 Bit	80/80/75/65	6 O'Clock	-30~80 -30~80	289.47 x 222.00 x 11.85 246.00 x 184.50
12.10'	ITLT1201SVLF46ZM Integrated 4 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	360	24 Bit	80/80/75/65	6 O'Clock	-30~80 -30~80	279.00 x 209.00 x 10.55 246.00 x 184.50
12.10'	ITLT1210SVLF45ZL Integrated 4 Wire RTP	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	360	24 Bit	80/80/75/65	6 O'Clock	-30~80 -30~80	279.00 x 209.00 x 10.55 246.00 x 184.50
12.10'	ITLT1210WXLN42CM	LVDS	WXGA 1280x800 16:9 Normally Black, Transmissive	400	24 Bit	85/85/85/85	6 O'Clock	-10~70 -20~80	278.00 x 184.00 x 8.16 261.12 x 163.20
12.10'	ITLT1210XGLV17ZM Integrated 5 Wire RTP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	400	24 Bit	80/80/60/80	6 O'Clock	-30~85 -30~85	279.00 x 209.00 x 9.00 245.76 x 184.32
12.10'	ITLT1210SVLN42ZM	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	450	24 Bit	80/80/75/65	6 O'Clock	-30~85 -30~85	279.00 x 209.00 x 9.00 246.00 x 184.50

Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
12.10'	ITLT1210XGLN13AM	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	500	24 Bit	80/80/60/80	6 O'Clock	-30~80 -30~80	279.00 x 209.00 x 9.00 245.76 x 184.32
12.10'	ITLT1210SVLN51ZH	LVDS	SVGA 800x600 4:3 Normally White, Transmissive	1000	24 Bit	80/80/75/65	6 O'Clock	-30~80 -30~80	279.00 x 209.00 x 9.00 246.00 x 184.50
12.10'	ITLT1210XGLN17GH	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	1000	24 Bit	80/80/70/70	6 O'Clock	-30~80 -30~80	279.00 x 209.00 x 9.00 245.76 x 184.32
15.00'	ITLT1500XGLP16CL Integrated PCAP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	200	24 Bit	80/80/70/70	6 O'Clock	-30~80 -30~80	339.10 x 262.15 x 14.60 303.00 x 228.00
15.00'	ITLT1500XGLV15CL Integrated 5 Wire RTP	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	200	24 Bit	80/80/70/70	6 O'Clock	-30~80 -30~80	339.10 x 262.15 x 14.20 303.00 x 228.00
15.00'	ITLT1500XGLN12CL	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	250	24 Bit	80/80/70/70	6 O'Clock	-30~80 -40~85	326.50 x 235.30 x 11.80 304.10 x 228.10
15.00'	ITLT1500XGLN17BE	LVDS	XGA 1024x768 4:3 Normally White, Transmissive	1500	24 Bit	80/80/70/70	6 O'Clock	-30~80 -30~80	326.00 x 255.00 x 11.80 304.10 x 228.10
15.60'	ITLT1560WXLN31AL	LVDS	XGA 1366x768 16:9 Normally White, Transmissive	300	24 Bit	85/85/80/80	6 O'Clock	-10~50 -20~60	363.80 x 215.90 x 16.85 344.20 x 193.50
15.60'	ITLT1560WXLN32AM	LVDS	XGA 1366x768 16:9 Normally White, Transmissive	420	24 Bit	85/85/80/80	6 O'Clock	-10~50 -20~60	363.80 x 215.90 x 16.85 344.20 x 193.50
17.00'	ITLT1700SXLN32ZH	LVDS	XGA 1280x1024 5:4 Normally White, Transmissive	600	24 Bit	85/85/80/80	6 O'Clock	-30~85 -30~85	358.50 x 296.50 x 18.00 337.92 x 270.34
17.00'	ITLT1700SXLP36GH Integrated PCAP	LVDS	SXGA 1280x1024 5:4 Normally White, Transmissive	1000	24 Bit	85/85/80/80	6 O'Clock	-30~85 -30~85	379.92 x 312.34 x 22.10 337.92 x 270.34
18.50'	ITLT1850HDLP23GM Integrated PCAP	LVDS	WXGA 1366x768 16:9 Normally White, Transmissive	240	24 Bit	85/85/80/80	6 O'Clock	-20~60 -20~50	445.00 x 265.60 x 19.22 409.80 x 230.40
18.50'	ITLT1850HDLN21GM	LVDS	WXGA 1366x768 16:9 Normally White, Transmissive	300	24 Bit	85/85/80/80	6 O'Clock	-20~50 -20~60	430.40 x 254.60 x 16.40 409.80 x 230.40
18.50'	ITLT1850HDLN13GH	LVDS	WXGA 1366x768 16:9 Normally White, Transmissive	650	24 Bit	85/85/80/80	6 O'Clock	-20~50 -20~60	430.40 x 254.60 x 10.50 409.80 x 230.40
18.50'	ITLT1850HDLP25GH Integrated PCAP	LVDS	WXGA 1366x768 16:9 Normally White, Transmissive	800	24 Bit	85/85/80/80	6 O'Clock	-20~60 -20~50	445.00 x 265.60 x 19.22 409.80 x 230.40
19.00'	ITLT1900SXLF42ZM Integrated 5 Wire RTP	LVDS	SXGA 1280x1024 5:4 Normally White, Transmissive	280	24 Bit	85/85/80/80	6 O'Clock	-0~50 -20~60	396.00 x 324.00 x 20.15 376.30 x 301.10



Size	Product ID	I/F	Display Resolution Display Mode	Nits	Color Depth	View Angle	View Direction	Op Temp St Temp	Outer Dimensions (mm) Active Area (mm)
19.00'	ITLT1900SXLN41AM	LVDS	SXGA 1280x1024 5:4 Normally White, Transmissive	350	24 Bit	88/88/85/85	6 O'Clock	-0~50 -20~60	396.00 x 324.00 x 17.80 376.30 x 301.10
19.00'	ITLT1900SXLN51AM	LVDS	XGA 1280x1024 5:4 Normally White, Transmissive	350	24 Bit	85/85/80/80	6 O'Clock	-30~85 -30~85	396.00 x 324.00 x 15.18 376.30 x 301.10
19.00'	ITLT1900SXLN43GH	LVDS	SXGA 1280x1024 5:4 Normally White, Transmissive	550	24 Bit	88/88/85/85	6 O'Clock	-0~50 -20~60	396.00 x 324.00 x 17.80 376.30 x 301.10
19.00'	ITLT1900SXLN44BE	LVDS	XGA 1280x1024 5:4 Normally White, Transmissive	1200	24 Bit	88/88/80/85	6 O'Clock	-20~70 -30~80	396.00 x 324.00 x 17.80 376.30 x 301.10
21.50'	ITLV2150HDLN12AM	LVDS	HD 1920x1080 16:9 MVA Normally Black, Transmissive	300	24 Bit	89/89/89/89	Free IPS	-20~60 -20~60	495.60 x 292.20 x 17.35 476.64 x 268.11
21.50'	ITLV2150HDLN22BH	LVDS	Full HD 1920 x 1080 MVA Normally Black, Transmissive	1200	24 Bit	89/89/89/89	Free MVA	-20~70 -30~70	495.60 x 292.20 x 17.35 476.64 x 268.11
21.50'	ITLV2150HDLN33BH	LVDS	HD 1920x1080 Normally Black, Transmissive	1200	24 Bit	89/89/89/89	Free MVA	-20~70 -30~70	495.60 x 292.20 x 10.50 476.64 x 268.11