

Home > Pro Audio / Broadcast > Direct Boxes and Adapters > Inline Audio Adapters

AUDIOSTIX



AudioStix are the newest additions to our expanding line of premium pro audio products. They can be used as stand-alone adapters, rear mounted into our modular QGPK Series rack panels, or permanently installed into any number of custom racks and wall plates. AudioStix are made in the USA.

318BT Bluetooth Receiver Introduction Video

Switchcraft Audiostix® 318BT Phantom Po... [▶](#)






318BT Latency Test Video

Switchcraft 318BT Latency Test [▶](#)








Questions? Contact Switchcraft Customer Support at 1-773-792-2700

Product	Description	
314DI		1/4" Feed Thru, Locking Male XLR, Ground Lift Switch and -20db Pad
318BT		Bluetooth Audio receiver, Phantom Powered, 3pin XLR Output to Mixer/Audio Console
318		1/8" Stereo Jack to Balanced, Mono 3-Pin Male XLR with Volume Control and Ground Lift Switch. (MIC Level Output)

Downloads:

318BT Quick Guide
Product Bulletin

319		1/8" Stereo Jack to Balanced, Mono 3-Contact Terminal Block with Pad and Ground Lift Switch. (Line Level Output)	BUY	IN STOCK
366R		AES-EBU Adapter (110 to 75 Ohm), Female XLR to BNC	BUY	IN STOCK
367R		AES-EBU Adapter (75 to 110 Ohm), BNC to Male XLR	BUY	IN STOCK
370DI		Passive A/V Direct Box - Inputs: RCA, 3.5mm; Output: Locking Male 3 pin XLR; Ground Lift & -20db Pad	 BUY	

Switchcraft : 773-792-2700 | Conxall : 630-834-7504 | Hostway



[Home](#) [Support](#) [Contact Us](#) [Login](#)