



LATITUDE 7300 ANNIVERSARY EDITION

Sustainable inside and out



PREMIUM MOBILITY OF THE 7000 SERIES

Work from anywhere with the smallest 13" notebook in its class.²⁰ Dell ExpressConnect intelligently finds the best Wi-Fi access point for less drops and lags. The latest 8th Generation Intel® vPro™ processors increase productivity, manageability, and security; while built-in SafeScreen and camera shutter options ensure privacy when working remotely.



MORE RECLAIMED CARBON FIBER, LESS WEIGHT

Dell has prevented over 2 million pounds of carbon fiber from ending up in landfills by using reclaimed carbon fiber. As the first PC manufacturer to pioneer this process,¹⁷ Dell continues to drive innovation with the 7300 AE. Partnering with small business, Carbon Conversions, an entirely new process was engineered to utilize reclaimed carbon fiber within the lid, advancing the total recycle content to 18.8%. The result is a premium laptop that's up to 24 grams lighter¹⁸ and meets Latitude's rigorous durability standards.



3.2M ↓
miles

END-TO-END SUSTAINABILITY

The Latitude 7300 Anniversary Edition attains EPEAT 2018 Silver and has more sustainable features than any other Latitude¹⁶. It comes with a long life cycle battery to increase the battery life for less replacements. Ocean-bound plastic (25%) and recycled HDPE plastic (75%) are used in the commemorative 25-year anniversary packaging trays, and a majority of units are shipped by sea. In partnership with The Conservation Fund, Dell is protecting a portion of the Garcia River Forest in Northern California in perpetuity. The carbon footprint offset is equivalent to 3.2 million miles driven.²¹



89% ↓

A LEADER USING WATERBORNE PAINT

Waterborne paint is used in 100% of the painted parts of this Anniversary Edition product to reduce VOC emission by 89%.¹⁹ Dell is a leader in this PC manufacturing process that aims to create a healthier work environment, enabling our supply chain to be more sustainable and bringing the best of our innovations into our products at scale.

Recommended Accessories

LATITUDE 7300 ANNIVERSARY EDITION

ON-THE-GO

ECO-FRIENDLY. TECH-SAVVY.

Make a positive impact with Dell's carrying cases designed with the Earth in mind.

Dell's EcoLoop solution dyeing process generates up to 90% less wastewater, 62% less CO2 emissions, and uses up to 29% less energy than traditional dyeing processes.* Further protect the environment and your electronic devices with an incredible water-resistant protective coating derived from reclaimed automobile windshields.



DELL PREMIER SLIM
BACKPACK 15 | PE1520PS

Made using earth-friendly dyes, this weather-resistant backpack is slim & sophisticated. It's constructed of sleek matte black and premium accents for a luxurious look and feel.

DELL'S EARTH-FRIENDLY
SOLUTION DYEING PROCESS*

90% less waste water
29% less energy usage
62% less CO2 emmissions



DELL PRO SLIM
BRIEFCASE 15 | PO1520CS

Designed with eco-friendly material through a process that reduces carbon emissions. Travel in style and comfort while benefiting the environment..



DELL USB-C MOBILE
ADAPTER | DA300

Connect your Latitude to almost any device with a convenient 6-in-1 compact adapter.



DELL PREMIER WIRELESS
MOUSE | WM527

Enhance daily performance and productivity with this elegantly designed wireless mouse.



DELL PRO STEREO
HEADSET | UC350

Hear every word clearly on your next call with the Dell Pro Stereo Headset, optimized to provide in-person call quality and certified for Microsoft Skype for Business.

AT THE DESK



DELL THUNDERBOLT
DOCK | WD19TB

Work at full speed with Dell's powerful Thunderbolt Dock. Charge your system faster, support up to three 4K displays and connect to your peripherals via a single cable.



DELL DUAL MONITOR
STAND | MDS19

This space-saving stand, mounts up to two 27-inch monitors, providing the screen real estate you need to be most productive.



DELL ULTRASHARP 27
MONITOR | U2718Q

The world's first 27" 4K monitor with InfinityEdge that supports HDR content playback. See stunning colors and details on a virtually borderless display.



DELL PREMIER
WIRELESS KEYBOARD
AND MOUSE | KM717

Enhance productivity and enjoy its elegant design that will fit into almost any workspace. For increased productivity you can simultaneously pair up to two compatible devices with Bluetooth LE.

Built for business

Dell Technologies Unified Workspace

Dell Technologies Unified Workspace is the most comprehensive solution to deploy, secure, manage and support virtually all devices from the cloud. We designed this revolutionary solution with intelligence and automation providing visibility across the entire endpoint environment. We help save time, improve user experience, optimize resources and strengthen security.



DEPLOY

Our modern deployment solution, ProDeploy in the Unified Workspace allows you to revolutionize the way deployment gets done. By spending just one hour for set up, IT can then hand deployment to Dell and have preconfigured systems shipped directly to the end users - wherever they are.



SECURE

Dell Endpoint Security for the Unified Workspace helps manage growing cyber risks while embracing workforce transformation. Gain actionable insight to help quickly and efficiently prevent, detect and respond to cyber-attacks-keeping your environment free from harm.



MANAGE

We integrated our hardware management solution Dell Client Command Suite with VMware Workspace ONE, allowing you to take advantage of unified endpoint management (UEM) and manage the firmware, operating system and applications for all devices from the Workspace ONE console. UEM simplifies the management of the entire environment saving IT time from having to work between separate consoles for PCs and phones.



SUPPORT

ProSupport Plus continues to be the only predictive and proactive support in the market. When compared to key competitors, ProSupport Plus with SupportAssist reduced time to resolve a failed hard drive with up to 11x faster time to resolution.

*Based on a Principled Technologies test report, "Spend Less Time and Effort Troubleshooting Laptop Hardware Failures" dated April 2018. Testing ommisioned by Dell, conducted in the United States. Actual results will vary. Full report: <http://facts.pt/L52XKM>

Features & Technical Specifications

LATITUDE 7300 ANNIVERSARY EDITION

Feature	Technical Specification	Feature	Technical Specification
Processor Options ¹	8 th Generation Intel® Core™ i5-8365U Processor (Quad Core, 6M Cache, 1.7GHz, 15W vPro)	Ports, Slots ¹	1 x Thunderbolt™ 3 with Power Delivery and DisplayPort 2 x USB 3.1 Gen 1 (one with PowerShare) 1 x HDMI 1.4 1 x Touch Fingerprint Reader (in power button) uSD 4.0 Memory card reader DC-in 7.4 mm barrel Wedge-shaped lock slot
Operating System ¹	Windows 10 Pro 64 bit	Materials and Color	LCD Cover - Carbon Fiber Weave (Standard) Color: Fiber Clear
Memory Options ^{1,2,3}	DDR4 2666 MHz Non-ECC SDRAM operates at 2400 MHz with Intel® 8 th Gen processors 2 DIMM 1x16GB	Dimensions & Weight ^{1,15}	Width: 12.06" / 306.50mm Depth: 8.14" / 206.96mm Height (non-touch): 0.67" ; 0.73" / 18.45mm (back) Weight: 2.90lbs/1.32kg 60Whr LCL battery, M.2 SSD, non-touch FHD, UMA, Carbon Fiber
Chipset ¹	Integrated with the Processor	Regulatory and Environmental Compliance ¹	Regulatory Model: P99G Regulatory Type: P99G001 ENERGY STAR ¹ EPEAT Registered. For specific country participation and rating, please see www.epeat.net BFR/PVC free ⁹
Intel Responsiveness Technologies ^{1,7}	Intel® Rapid Storage Technology	Input ¹	Single Pointing, spill resistant, backlit Keyboard Microsoft® Precision Touchpad
Graphics ^{1,13}	Intel® UHD Graphics 620 (8 th Gen Intel® Core™)	Systems Management ¹	Intel® vPro™ Technology (iAMT 12) (optional) Dell Client Command Suite available (dell.com/command), Factory Installed Dell Client Command Update, Dell Command Power Manager
Display ¹	13.3" FHD (1920 x 1080) Anti Glare, Super Low Power, (16:9) WLED, 300 nits, No Camera/Mic only, WLAN Capable, Carbon Fiber back, Non Touch	Warranty and Service ¹	Limited Hardware Warranty ⁴ Standard 3 year Mail-in Service after Remote Diagnosis ¹¹ optional 4 and 5 year hardware warranty extensions and 4-5 year Dell ProSupport contracts available ¹²
Storage Options ^{1,5}	256GB PCIe NVMe SSD (Class 40)	Peripheral Ecosystem ¹	Purpose built ecosystem to enable productivity on the go or at the desk. Includes Dell Dock-WD19, Dell Power Companions, Dell Professional Briefcases, Dell 24" & 27" Monitors, and Dell Wireless Keyboard and Mouse
Security ¹	TPM 2.0 FIPS 140-2 Certified, TCG Certified fingerprint reader in power button Dell Client Command Suite Optional Dell Data Security and Management Software Dell Endpoint Security Suite Enterprise Dell Data Guardian Dell Encryption Enterprise Dell Encryption Personal Dell Threat Defense MozyPro® or MozyEnterprise® RSA NetWitness® Endpoint RSA SecurID Access VMware Workspace ONE Absolute® Endpoint Visibility and Control		
Docking ¹	Dell Thunderbolt™ Dock - WD19TB (optional, sold separately) Dell Dock - WD19 (optional, sold separately)		
Optical Drive Options	External Options Only		
Multimedia ¹	High Quality Speakers Universal Audio jack Noise reducing array microphones Optional RGB HD Camera with Dell Privacy Shutter Skype For Business Certified		
Battery Options ^{1,5}	4 cell 60 WHr Long Life Polymer		
Power Options ¹	65W adapter, 7.4mm barrel 65W BFR/PVC Halogen Free adapter, 7.4mm barrel 65 Watt Rugged Adapter 7.4mm barrel - India 90 Watt AC Adapter 7.4mm barrel 65W adapter, Type-C 90W adapter, Type-C		
Connectivity options ^{1,14}	Intel® Dual-Band Wireless-AC 9560 Wi-Fi + Bluetooth 5.0 Wireless Card (2x2). Bluetooth Optional		



LATITUDE 7300 ANNIVERSARY EDITION

Sustainable inside and out

1 Offering may vary by country and by configuration

2 A 64-bit operating system is required to support 4GB or more of system memory.

3 GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less.

4 Limited Hardware Warranty: For copy of Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty

5 Battery support is dependent upon graphics support. Check technical guides for detailed support

6 COMPUTRACE Not a Dell offer. Certain conditions apply. For full details, see terms and conditions at www.absolute.com/en/about/legal/agreements.

7 Intel Rapid Storage Technology requires a HDD, mSATA, or an SSD, as primary storage device and Windows OS required

8 Wireless antenna available only at time of system purchase

9 Dell Latitude 7000 Series are brominated flame retardant free (BFR-free) and polyvinyl chloride free (PVC-free); meeting the definition of BFR-/PVC-free as set forth in the iNEMI Position Statement on the 'Definition of Low-Halogen Electronics (BFR-/CFR-/PVC-free)'. Plastic parts contain less than 1,000 ppm (0.1%) of bromine (if the Br source is from BFRs) and less than 1,000 ppm (0.1%) of chlorine (if the Cl source is from CFRs or PVC or PVC copolymers). All printed circuit board (PCB) and substrate laminates contain bromine/chlorine total less than 1,500 ppm (0.15%) with a maximum chlorine of 900 ppm (0.09%) and maximum bromine being 900 ppm (0.09%).

10 Mobile Broadband Subject to service provider's broadband subscription and coverage area; additional charges apply.

11 Onsite Service after Remote Diagnosis: Remote Diagnosis is determination by online/phone technician of cause of issue; may involve customer access to inside of system and multiple or extended sessions. If issue is covered by Limited Hardware Warranty (www.dell.com/warranty) and not resolved remotely, technician and/or part will be dispatched, usually within 1 business day following completion of Remote Diagnosis. Availability varies. Other conditions apply.

12 Dell Services: Availability and terms of Dell Services vary by region. For more information, visit www.dell.com/servicesdescriptions.

13 GB means 1 billion bytes and TB equals 1 trillion bytes; significant system memory may be used to support graphics, depending on system memory size and other factors.

14 Miracast Wireless Technology: Requires a compatible media adapter (sold separately) and an HDMI-enabled display.

15 Weights vary depending on configuration and manufacturing variability.

16 Based on August 2019 internal analysis. Most sustainable based on EPEAT Points and use of sustainable materials and processes in product and packaging.

17 Based on internal analysis, Sept. 2019. Total reclaimed carbon fiber calculated from 2015 through 2018.

18 Compared to Dell Latitude 7300, Sept. 2019.

19 Compared to previous generation system that used solvent-based paint and no waterborne paint. Based on internal analysis, Sept. 2019.

20 Based on Dell Footprint Area (X * Y) internal analysis, April 2019.

21 The carbon footprint for the Latitude 7300 25th AE is based on the Life Cycle Assessment Report by thinkstep AG, July 2019. Following a rigorous project registration process used to ensure the originating offset project contributes to real and additional emission reductions, 1333 offset credits issued by the Climate Action Reserve were retired by The Conservation Fund on behalf of Dell on October 23, 2019. Equivalent calculated using: <https://www.epa.gov/energy/greenhouse-gas-equivalencies-calculator>.

* Based on Dell internal analysis of published data on solution-dyed virgin polyester and fabric supplier data sheets, December 2018.