




## Bestückungsplan / Contact layout



■ bestückt / assembled

## Leiterplatten- Lochbild / PCB drillhole pattern



Elastische Einpresszone mit Übergabestreckzone /  
compliant pressfit zone with mating transfer zone  
Isolierwerkstoff / housing material : PBT GF30  
Bauart 7 / type 7

Anforderungsstufe 2 = 400 Steckzyklen / performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2



**Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2**

Schichtaufbau im metallisierten Loch siehe Zeichnung 164062/Nr.6

diameter of drilled hole see drawing 164062/No.6

1)  $\overset{+0,09}{\phi 10}$  Durchmesser des metallisierten Loches

1)  $\varnothing 1,0_{-0,06}^{+0,09}$  Durchmesser des metallisierten Loches

Information:		Tolerances		 Scale 2:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation  <b>Federleiste B/2, 32 EE</b>  <i>Fem.Connector B/2, 32 Pressfit</i>	
		<a href="http://www.ERNI.com">www.ERNI.com</a>		<b>284895</b>  I	
Index	Date	Class		STVB/2  <b>A3</b>	