

JOIN OUR NEWSLETTER



SEARCH



BROWSE BY
**PRODUCT
CATEGORY**



BROWSE BY
**DEVICE
MANUFACTURER**



ADVANCED
**INDUSTRIAL
SEARCH**

[Home](#) / CUSTOM-332



hover to zoom; click to enlarge

PART#: CUSTOM-332

Chemistry:	Nickel Cadmium (NICD)
Voltage:	1.2
Capacity:	900mAh
Measurements:	1.9" x 0.56" 48.26mm x 14.22mm

[Find a Distributor](#)

This replacement 1.2 Volt 900 mAh Nickel Cadmium battery is used in Emergency lighting and meets or exceeds original manufacturer specifications.

SPECIFICATIONS

Shipping Weight (oz)	0.9000
Manufacturer	Dantona
Warranty	6
UPC	728286974944
Length	1.9" (48.26mm)
Width	No" (0.00mm)
Height / Diameter	0.56" (14.22mm)
Voltage	1.2
mAh	900
Number of Cells	1
Battery Chemistry	Nickel Cadmium (NICD)
Rechargeable	Rechargeable
Qty Per Package	1
Type of Cell	AA, Cylindrical
Weight	0.9 oz

Compatible Batteries and Devices

[Batteries \(5\)](#)
[Devices \(2\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been sponsored or approved by any of such manufacturers. Any trademarks or model numbers listed in this catalog are identified for compatibility or cross-reference purposes only.

**CAN'T FIND
THE BATTERY
YOU NEED?**

**CALL US AT
1-800-Dantona
TO SPEAK TO
A BATTERY EXPERT**



**VIEW OUR WIDE
SELECTION OF**

**Custom
Battery
Packs**

[SHOP OUR CUSTOM PACKS](#)

