



President's Day Deals: Save up to 40% on electronics and accessories

[Home](#) > [For Home](#) > [Accessories](#) > [Networking](#) > ... > [Transceivers & Direct Attach Cables](#)
> [PowerEdge SFP+, 10GbE SR/SX, Optical Transceiver, LC Connector, for Intel and Broadcom,CusKit](#)

PowerEdge SFP+, 10GbE SR/SX, Optical Transceiver, LC Connector, for Intel and Broadcom,CusKit

★★★★★ (0) [Be the first to write a review](#)

☐ Add to Compare

The Dell™ short-wavelength SFP+ transceiver delivers fiber connectivity to extend the range of your network. This hot-pluggable transceiver with SFP+ (Small Form Factor Pluggable) footprint features duplex LC connector and provides up to 10 Gbp ... [Show More](#)

Manufacturer part 519N7
Dell part 407-BBOK

Standard Delivery Free

Dell Price

Financing [As low as /mo.^](#)
[Apply](#)

★ Up to back in rewards

Ships in 3-4 Days

Order Code 407-bbok

Add to Cart



Overview

Tech Specs &
Customization

Ratings & Reviews

Support

The Dell™ short-wavelength SFP+ transceiver delivers fiber connectivity to extend the range of your network. This hot-pluggable transceiver with SFP+ (Small Form Factor Pluggable) footprint features duplex LC connector and provides up to 10 Gbps bi-directional data transfer rate. The transceiver complies with Gigabit Ethernet as specified in IEEE 802.3 and Fiber Channel FC-PH, PH2, PH3 and FC-PI 10.0. Additionally, it provides a unique enhanced digital diagnostic monitoring interface, which allows real-time access to device operating parameters such as transceiver temperature, laser bias current, transmitted optical power, received optical power, and transceiver supply voltage.

- Provides up to 10 Gbps bi-directional data links
- Duplex LC connector
- Hot-pluggable SFP+ footprint
- Built-in digital diagnostic functions
- This SKU is also compatible with these SKU's 330-8723, 9272Y, R8H2F and 519N7

Tech Specs & Customization

Form Factor

Plug-in module

Device Type

SFP+ transceiver module - LC

Ports Qty

2

Data Link Protocol

Gigabit Ethernet, 10 Gigabit Ethernet, 10Gb Fibre Channel

Cabling Type

10GBase-SR

Max Transfer Distance

1640 ft

Ratings & Reviews

★★★★★ (0)

Have your say

Sign in from the main menu to write a review

Support



Dell Support

From drivers and manuals to diagnostic tools and replacement parts, Dell Product Support has you covered!

Get Started



Quick. Simple. Financing.^

Financing for qualified customers with Dell Preferred Account.^



Free Shipping & Price Match Guarantee

Enjoy free shipping, easy returns and price match guarantee.



Dell Advantage Rewards

Join for free to get up to 5% back in rewards* and free expedited delivery.

