

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732511851

Status:

Active

Overview:

Precision Compression-Mount Microwave Test Connectors

Description:

50 Ohms, Precision Test Connector, Optimized SMA Jack, Two Hole Flange with 2 Screws 4.76mm, 0-80 Threads



Documents:

[Drawing \(PDF\)](#)

[HFSS Model](#)

[3D Model](#)

[3D Model \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	RF/Coax Connectors
Series	73251
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Style	PCB
Type	Subminiature
UPC	822350628181
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	1.990/g
Orientation	Straight
PCB Mounting	Surface Mount
PCB Thickness - Recommended	3.05mm
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Flange
Reverse Polar	No
Electrical	
Frequency	27 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73251-185-000

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

50 Image

Compliant with Exemption 3

Not Contained

China ROHS

ELV

RoHS Phthalates

Search Parts in this Series

73251 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION