

5

4

3

2


1

D


C

B


A



Max torque = 0,4 N.m
(4 screws)



Cable reduction
plate (x2)



Minimum cable diameter: 3

Maximum cable diameter:

- with rubber bushing: 9,7
- without rubber bushing: 12
- without reduction plate: 15

				Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 50 poles, top entry, straight metal hood	Maßstab/ Scale 1:1
			Detail.	15/04/02	CV			
EC00368	07/07/09	PK	Insp.					
33932	15/01/07	PK	Stand.					
31069	30/07/02	CV	HARTING EURL F-95972 Paris				TB 09 67 050 034X	Blatt/ Page 1 / 1
29769	15/04/02	CV						
Mod.	Dot.	Name				Sub.		

09 67 050 0349	M3
09 67 050 0344	4-40 UNC-2A
Part number	Screw thread