



Part Number : [640038070](#)

Product Description : Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG

Series Number : 207126

Status : Active

Product Category : Applicators and Crimp Modules



Documents & Resources

Tooling Specifications

[ATS-638161100-001.pdf](#)

[ATS-640038070-001.pdf](#)

[TM-638161000-001.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Battery Cable Lug,VersaKrimp
Tool Type	Crimp Module
UPC	889056282895
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Mates With / Use With

Use with Part(s)

Description	Part Number
Crimp Adapter For DIN Style Dies in Molex Pneumatic Universal Crimp Machine	<u>638018901</u>
Power Crimp Head for Din Style Crimp Dies	<u>638161100</u>

Applicable Parts

Description	Part Number
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton	<u>191930325</u>
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 7/16" (M11), Carton	<u>191930329</u>
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton	<u>191930330</u>
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	<u>191930331</u>
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Carton	<u>191930333</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton	<u>191930341</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton	<u>191930342</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	<u>191930345</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed	<u>191930346</u>

Barrel, Stud Size 5/16" (M8), Carton	
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 7/16" (M11), Carton	<u>191930348</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton	<u>191930350</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/4" (M18), Carton	<u>191930351</u>
VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 5/8" (M16), Carton	<u>191930352</u>
VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton	<u>191930612</u>
VersaKrimp Parallel Splice for 1/0 AWG Wire	<u>192050009</u>
VersaKrimp Parallel Splice for 2/0 AWG Wire	<u>192050010</u>
VersaKrimp Butt Splice for 1/0 AWG Wire	<u>192150047</u>
VersaKrimp Butt Splice for 2/0 AWG Wire	<u>192150048</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/4" (M6), Plated	<u>192210234</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 5/16" (M8), Plated	<u>192210240</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/8" (M9), Plated	<u>192210241</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/2" (M12), Plated	<u>192210242</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/16" (M8), Plated	<u>192210243</u>
Compression Style Ring Tongue	<u>192210244</u>

Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Plated	
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Plated	<u>192210245</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 3/8" (M9), Unplated	<u>192210377</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Unplated	<u>192210379</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/2" (M12), Unplated	<u>192210393</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 5/16" (M8), Unplated	<u>192210394</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Unplated	<u>192210397</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/16" (M8), Unplated	<u>192210398</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/4" (M6), Plated	<u>192210422</u>
Compression Style Ring Tongue Terminal for 1/0 AWG Wire, Stud Size 1/4" (M6), Unplated	<u>192210423</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/8" (M16) Unplated	<u>192210597</u>
Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 5/8" (M16), Plated	<u>192210598</u>

This document was generated on Sep 16, 2025