


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A5	NEW RELEASE	03/DEC/2021	
A6	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A7	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER





NOTE:
1. TESTING CONDITIONS:
   A: INSULATION RESISTANCE: 10MΩ
   B: VOLTAGE: DC300V/0.01S
   C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
   DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

P1	P2	P1	P2
1	1 BLACK	9	9 GREY
2	2 BROWN	10	10 WHITE
3	3 RED	11	11 PINK
4	4 ORANGE	12	12 LIGHT GREEN
5	5 YELLOW	13	13 BLACK/WHITE
6	6 GREEN	14	14 BROWN/WHITE
7	7 BLUE	15	15 RED/WHITE
8	8 PURPLE	SHELL	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDMDB15MF-001.5	1.5FT±0.8inch	457±20mm
CS-DSDMDB15MF-002.5	2.5FT±1inch	762±25mm
CS-DSDMDB15MF-005	5FT±2inch	1524±51mm
CS-DSDMDB15MF-010	10FT±3inch	3048±76mm
CS-DSDMDB15MF-015	15FT±3inch	4572±76mm
CS-DSDMDB15MF-016	16FT±3inch	4877±76mm
CS-DSDMDB15MF-020	20FT±4inch	6096±102mm
CS-DSDMDB15MF-025	25FT±4inch	7620±102mm
CS-DSDMDB15MF-035	30FT±6inch	10668±152mm
CS-DSDMDB15MF-050	50FT±8inch	15240±203mm

NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
DECIMALS: .X ±.X; .XX ±.XX; .XXX ±.XXX
ANGLES: ±X°

THIRD ANGLE PROJECTION

EAR NO.

APPROVALS	DATE
DRAWN XF	
CHECKED HYJ	
RESP ENG	
MFG ENG	

CAD FILE:

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

DELUXE DB15M/F MOLDED

SIZE A | DWG. NO. CS-DSDMDB15MF-XXX | REV. A7

SCALE: N/A | SHEET 1 OF 1

Downloaded from Arrow.com.