

REV.	DESCRIPTION	DATE
A	RELEASE	2016.06.08

RoHS

MATERIAL&FINISH

Insulator: PBT Glass Fiber (UL94V-0)

Contact Material: Terminal Brass.

Shell Spec.

Contact Plating : Terminal Gold-Plated Over Nickel.

Shell Nickel.

SPECIFICATIONS

Current Rating :1A AC, DC









Voltage Rating : 250V AC, DC

Temperature Range:-40° C To+105° C

Contact Resistance:20M Ω Max

Insulation Resistance:1000M Ω Min

Withstanding Voltage:500V AC/Min



NUMBER OF POSITIONS	DIMENSION				
	A	B	C	D	E
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.48
37	69.32	63.50	54.75	49.86	45.72

UNLESS TOLERANCE		DRAW		Cnc Tech,LLC	
GENERAL	ANGLE	DESIGN	BY		
X. ± 0.30	X.° ± 3.0°	CHECK	BY		
.X ± 0.20	.X° ± 2.0°	APPROVE	BY		
.XX ± 0.15	.XX° ± 1.0°	400F0-XX-1-004S			
.XXX ± 0.08	.XXX° ± 0.5°				

Part NO.

400F0-XX-1-004S

SCALE	SHEET	UNIT	DRW NO:		REV: A
1:1	1/1	MM			