

1


2

3


4

5

RoHS Compliant



PIN OUT:



| PART NO.          | LENGTH    |
|-------------------|-----------|
| 105-1042-BL-00050 | L=500±30  |
| 105-1042-BL-00100 | L=1000±50 |
| 105-1042-BL-00150 | L=1500±50 |
| 105-1042-BL-00200 | L=2000±60 |

NOTE:

- 1.OPEN/SHORT/INTERMITTENCE: 100%
- 2.HI-POT: 50V AC/0.01S 50V DC/0.01S
- 3.INSULATION RESISTANCE: 10M OHM (MIN)
- 4.CONDUCTIVE RESISTANCE: 3 OHM (MAX)
- 5.CAPACITANCE DETECTION: 10nF±20% BETWEEN A1 AND A4

| ITEM | PART NO. | DESCRIPTION                                                                                   | Q'TY |
|------|----------|-----------------------------------------------------------------------------------------------|------|
| 1    | CABLE    | 2725 (30AWGX1P+EAM)*4+(32AWGX1P+AM)+32AWGX4C+24AWG(7/0.20)X2C+E+AEB85%<br>16/11/0.08 OD=4.8mm | A/R  |
| 2    | TYPE C/M | USB3.1 TYPE C/M PIN 30U" C1=10nF±20% INSULATOR BLACK,NICKEL PLATED SHELL                      | 1    |
| 3    | TYPE C/M | USB3.1 TYPE C/M PIN 30U" WITH IC C1=10nF±20% INSULATOR BLACK NICKEL PLATED SHELL              | 1    |
| 4    | PVC      | 55P PVC MOLDING COLOR:BLACK                                                                   | A/R  |

DRAWN:

CHECKED:

APPROVAL:

GENERAL TOLERANCE:

.X=±0.20


.XX=±0.15

UNIT: MM

SCALE:1:1

SHEET: 1 / 1

PROJECTION:

**CnC Tech**

Industrial Cable and Connector Technology

DESCRIPTION:

USB3.1 TYPE C TO USB3.1 TYPE C CABLE

PART NO:

105-1042-BL-00XXX-1

SIZE

A4

A 23-Mar-2021

REV DATE FILE BY