

## Han B Hood Side Entry 2 Levers PG 21



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 30 024 0530  |
| Specification      | Han B Hood Side Entry 2 Levers PG 21  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09300240530">https://b2b.harting.com/09300240530</a> |

### Identification

|                          |                    |
|--------------------------|--------------------|
| Category                 | Hoods/Housings     |
| Series of hoods/housings | Han <sup>®</sup> B |
| Type of hood/housing     | Hood               |
| Type                     | High construction  |

### Version

|                            |   |
|----------------------------|---|
| Size                       | 24 B  |
| Version                    | Side entry  |
| Cable entry                | 1x Pg 21  |
| Locking type               | Double locking lever (on the hood)                |
| Han-Easy Lock <sup>®</sup> | Yes   |
| Field of application       | Standard hoods/housings for industrial connectors |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65   |
|  | IP66   |
|  | IP67   |
| Type rating acc. to UL 50 / UL 50E     | 4  |
|  | 4X   |
|  | 12   |



Pushing Performance  
Since 1945

## Material properties

|  |   |
|--|---|
| Material (hood/housing)                                    | Aluminium die-cast  |
| Surface (hood/housing)                                     | Powder-coated   |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                                      |
| Material (locking)   | Polycarbonate (PC)<br>Stainless steel                     |
| Colour (locking)   | RAL 7037 (dust grey)                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0   |
| RoHS   | compliant   |
| ELV status   | compliant   |
| China RoHS   | e   |
| REACH Annex XVII substances                                | Not contained   |
| REACH ANNEX XIV substances                                 | Not contained   |
| REACH SVHC substances                                      | Yes   |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| California Proposition 65 substances                       | Yes   |
| California Proposition 65 substances                       | Nickel  |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                              |

## Specifications and approvals

|           |              |
|-----------|--------------|
| Approvals | CE<br>DNV GL |
|-----------|--------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 16.86 g                                  |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140047297                            |
| ETIM                           | EC000437                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |