
HellermannTyton

Technical data sheet

Article number:
170-10800 HEGP08



Product Group	Standard polyester braided sleeving
Product Family	Helagaine HEGP
Material	Polyester (PET)
Colour	Black (BK)

Application Method	To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0, see page
Bundle Ø max.	12 mm
Bundle Ø min.	5 mm
Melting Point	+250 °C
Operating Temperature	-50 °C to +150 °C
Package Content	100 m
Package Content packed in	meter
Specifications	ECE R-118-03 Abschnitt 6 / Annex 6, ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2

HF ✓ RoHS ✓

EN 45545-2 ECE R-118

created on 15. May 2026, 6:34 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.