

# FSP036-RHBN3

36 W AC/DC Adapter



## Features

36 W AC/DC Adapter

## Specifications

Environment	
Operating Temperature	0°C ~ 40°C
Storage Temperature	-20°C ~ 80°C
Input	
Voltage	90-264 VAC
Frequency	47-63 Hz
Input Current	1.8A
Inrush Current	3A
Output	
Voltage	12V
General	
Watt	36W
Efficiency	88.3%
Dimensions	37.8 x 89.8 x 27.0 (mm)

## Ordering Information

63040-010036-220-RS	Adapter Power;FSP;FSP036-RHBN3;9NA0362708;;Vin:90~264VAC;36W;Dim:37.8*89.8*27.0mm;Plu g=9.5mm;Cable=1500mm;Erp(NO LOAD 0.075W);Vout:12VDC;Ø2.5/Ø5.5;CCL;RoHS
63040-010036-210-RS	Adapter Power;FSP;FSP036-RHBN3;9NA0362707;;Vin:90~264VAC;36W;Dim:37.8*89.8*27.0mm;Plu g=7.5mm;Cable=1500mm;Erp(NO LOAD 0.075W);Vout:12VDC;Ø2.5/Ø5.5/lock;CCL;RoHS