

[May 2008] PRECI-DIP participation to exhibition 'Arrow Global Village' in Helsinki (Finland)
More >>

[April 2008] PRECI-DIP SA and its local distributor SEMICON

YOUR SELECTED PRODUCT

For other versions than the listed available standard types, please contact PRECI-DIP

SPECIFICATIONS:
SMD spring loaded contact
- Press-in mount into dia 1.58 mm hole
- Materials: body + piston brass, spring stainless steel
- Electrical contact resistance max. 20 milliohms
- Mechanical life min. 40'000 cycles

AVAILABLE STANDARD TYPES

Ordering Part Number		Height	Stroke
90023-AS	RoHS	4.5 mm	1.4 mm

<< Back