

[The company](#)
[Products](#)
[Articlefinder](#)
[Contacts](#)
[Distribution](#)
[Download](#)
[Service](#)

Connectors

[Customer specific solutions](#)
[D SUB](#)
[D SUB cover](#)
[D SUB accessories](#)
[DVI](#)
[Centronics](#)
[IDC](#)
[Modular](#)
[USB](#)
[IEEE 1394](#)
[Switches](#)
[Power supply](#)
[DIN 41612](#)
[DIN 41617](#)
[Mini DIN](#)
[IC Socket](#)
[Pin and female header](#)
[Jumper](#)
[Connector sleeves](#)
[Solder terminals](#)
[Test terminals](#)
[Terminal Blocks](#)
[Memory Card connectors](#)
[FFC / FPC connectors](#)
[Micro-Miniature](#)
[Thermal management](#)
[Cable assembly](#)


Pin and female header

AW 109/10-T
female-header 20pins THT 2,54mm 3A single
row 25,90mm straight Sn

Article number: AW 126 20 Z T

product group: pin-&female-header

style: female-header

contact type: THT

pin count: 20

spacing in mm: 2,54

current rating: 3A

version: single row

contact length: 25,90mm

contact direction: straight

plating: Sn

contact machining: turned contacts

packaging: polybag

process: THT

insulator: PBT UL94V-0

: AW 109/10-T

: #NV

» PDF download «