Part Number : 1301540065
Product Description : Super-Safeway Molded Y Cordset, 2 Pole/3 Wire SJOW Cordset, Cordset Length 0.91m (3.0'), NEMA L5-20, 125V, Inline GFCI
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 2647-Y-IN



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Super-Safeway Molded Y Cordset, 2 Pole/3 Wire SJOW Cordset, Cordset Length 0.91m (3.0'), NEMA L5-20, 125V, Inline GFCI
IP Rating	N/A
NEMA Configuration	NEMA L5-20
Product Name	Super-Safeway
Specialty	N/A
Type	Molded Y Cordset
UPC	78678839001

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
Voltage - Maximum	125V

Physical

Cord Type	12/3 SJOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	Yes
Poles	2-pole/3-wire
Receptacle Type	Duplex

Downloaded from Arrow.com.