





PIN ASSIGNMENT



Material:

- Cable: UL2919 28AWG 25P+ADB BE02
- OD: 9.0
- P1 & P2 Connectors: HPDB-50 Pin(BK)
- ID:0.62MM
- IDC Type Molding
- Hi TEAMP Tape W:20MM
- Inner Molding: PE-5321
- Foil: FOIL-CU-32MM
- Latches/BE02 (Flag Hooks)

Unit: MM

RoHS
Compliant

ITEM NO.

AK579/F-1

TITLE

SCSI Cable 2 - 1 Meter,
D-Sub 50HP Male <=> D-Sub 50HP Male

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
©Copyright 2010 by Assmann Electronic Components
All International Rights Reserved