




Color: ■ silver-colored Similar to illustration

Technical data

Suitable	for Eaton's push-button frame
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	1000 markers/reel; 1 line
Printing device	Smart Printer (thermal transfer printer)

Physical data

Height	26.5 mm
Width	18 mm
Depth	0.23 mm
Marking surface	26.5 x 18 mm

Mechanical data

Mounting type	Securing with cover (210-851)
Smear resistance	in conjunction with 258-5005 Ink Ribbon

Material data

Color	silver-colored
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	Light adhesive rubber coating (without adhesive)
Halogen-free	Yes
Weight	188 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		≥+22 °C
Ambient temperature (operation)		-30 ... +130 °C
Relative humidity		40 ... 50 %

Commercial data		
Product Group		2 (Terminal Block Accessories)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821674900
Customs tariff number		39191080888

Product Classification		
UNSPSC		55121612
eCl@ss 10.0		27-40-06-29
eCl@ss 9.0		27-40-06-29
ETIM 9.0		EC001288
ETIM 8.0		EC001288
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search		
Environmental Product Compliance 210-850		

Documentation

Operating Instructions			
210-852 Information on handling print material	1	pdf	1004.72 KB
	28.08.2020		



1 Compatible Products
1.1 System counterpart
1.1.1 Cover



[Item No.: 210-851](#)
Cover; For push-button label (210-850)
mounting; halogen-free; transparent

1.2 Required Accessories
1.2.1 Marking
1.2.1.1 Cover



[Item No.: 210-851](#)
Cover; For push-button label (210-850)
mounting; halogen-free; transparent