





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-19-001400	13FEB2019	GP	HR
	A2	ECR-19-009236	12 JUN2019	GP	HR
	B	ECR-19-018949	29NOV2019	GP	HR
	B1	ECR-20-001669	21FEB2020	GP	HR



- 1 PACKAGING ACCORDING SPEC. V-2311753
- 2 SPECIFIED WIRE RANGE: SEE 
-  3 SUPPLY CONDITION: LEVER AND CPA IN ENDOCK POSITION
-  4 SUPPLIER MARK
-  5 CAVITY IDENTIFICATION
-  6 PRODUCT-SPECIFICATION: TE-NO. 108-94749
-  7 APPLICATION-SPECIFICATION: TE-NO. 114-94518

1x	1x	1x	1x	0-2311758-1	LEVER	BLACK	6
1x	1x	1x	1x	0-2840616-1	CPA	RED	5
1x	1x	1x	1x	0-2311756-1	RETAINER FOR SEAL	BLACK	4
1x	1x	1x	1x	0-2310216-1	PERIPHERAL SEAL	GREEN	3
-	-	-	-	0-2311780-2	HVIL	-	-
-	-	-	-	0-2311757-1	EMI SHIELD	-	-
-	-	-	-	0-2311755-1	INNER HOUSING	-	-
1x	1x	1x	1x	0-2312685-1	INNER HOUSING ASSEMBLY	-	2
1x	-	-	-	0-2311754-4	OUTER HOUSING, COD D	ORANGE	1d
-	1x	-	-	0-2311754-3	OUTER HOUSING, COD C	ORANGE	1c
-	-	1x	-	0-2311754-2	OUTER HOUSING, COD B	ORANGE	1b
-	-	-	1x	0-2311754-1	OUTER HOUSING, COD A	ORANGE	1a
0-2311753-4 CODING D	0-2311753-3 CODING C	0-2311753-2 CODING B	0-2311753-1 CODING A	PART NO	DESCRIPTION	COLOUR	ITEM NO
B	B	B	B	REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)			
75.2	75.2	75.2	75.2	WEIGHT OF EACH ASSY NO [g]			
QTY REQD PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08SEP2017 SHREESHAIL CHK 08SEP2017 PARUSURAM APVD 27NOV2017 H. RIPPER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2POS PCON12 PLUG ASS'Y 180-DEGREE	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 	
				APPLICATION SPEC 	
MATERIAL - -		WEIGHT -		SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=2311753	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 1:1	
				SHEET 1 OF 1	
				REV B1	