

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DF

SO

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

RELEASED

1-24-07


CT

DE



1. MARKED PER MIL-STD-130.
2. TO MATE WITH AMP LGH-1/2L RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
3. OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000 FEET, -55°C TO +125°C.
4. TO MATE WITH ANY JEDEC-J1-21 CAP.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES [mm]

MATERIAL

SEE CALLOUTS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± .02 [0.5]
3 PLC	± .005 [0.13]
4 PLC	± -
ANGLES	± -

FINISH

SEE CALLOUTS

DWN C.C.THOMAS 1-24-07

CHK D.EABY 1-25-07

APVD D.EABY 1-25-07

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

AMPTyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

LEAD ASS'Y, POS STOP,
SGL. END, LGH-1/2L WITH J1-21 BOOT

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1883872

SCALE 2:1

SHEET 1 OF 1

REV A

1883872-1

PART NO.