
Data sheet

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 5.9 - 12.3 mm, 25.4 x 57 mm, white
Order No.	1768380000
Type	LM WO 25.4/57 WS
GTIN (EAN)	4032248110025
Qty.	10 items

Downloaded from Arrow.com.

Data sheet

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	57 mm	Width (inches)	2.2441 inch
Net weight	10 g		

Temperatures

Operating temperature range	-40…150 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Acrylate	
Material colour according to resistance code	9	
Number per sheet	35	
Type of printing	neutral	
Version	Self-adhesive	
Width	57 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	150 °C	
Operating temperature range, min.	-40 °C	
Colour	white	
Halogen	No	
Basic material	Polyester film	
Printed characters	without	
Number of markers per packaging unit	350	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of combinations per packaging unit	10
	Number of markers per combination	35
Size of labelling field	25.4 x 18 mm	
Number of markers per combination	1 Label sheet = 35 Conductor and cable markers	
Operating temperature range	-40…150 °C	

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	120 mm²
Conductor cross-section, min.	25 mm²	Conductor O.D., max.	12.3 mm
Conductor O.D., min.	5.9 mm	Text field width	25.4 mm
Text field height	18.5 mm	Conductor O.D.	5.9 - 12.3 mm
Cross-section for connected wire	25 - 120 mm²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		


Downloaded from Arrow.com.

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.