



Part Number : [1301080303](#)
Product Description : Industrial Duty LED Tube Light, 72W, Cord Type 16/3 SOOW, 1.22m (4.0') Cord Length, 1.22m (4.0') Lamp Length
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 2003LED



Documents & Resources

- Drawings**
[1301080303 sd.pdf](#)
- Specifications**
[PS-130108-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

- Compliance Statements
- EU RoHS
 - REACH SVHC
 - Low-Halogen

- Industry Documents
- IPC 1752A Class C
 - IPC 1752A Class D
 - Molex Product Compliance Declaration
 - IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Industrial Duty LED Tube Light, 72W, Cord Type 16/3 SOOW, 1.22m (4.0') Cord Length, 1.22m (4.0') Lamp Length
NEMA Configuration	NEMA 5-15
Product Name	Industrial Duty
Type	Wide Area Lamps
UPC	78172546823

Agency

UL	E174254
----	---------

Electrical

Lamp Wattage - Maximum	72W
Lumens	7200
On/Off Switch	No
Voltage (Fixture) - Maximum	120/277VAC 50/60 HZ

Physical

Bulb Type	T10 LED - 5500K
Cord Length - Primary	1.22m (4.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	101.60mm (4.000")
Duty	Industrial

Guard Included	Yes
Guard Type	Clear Butyrate
Height	101.60mm (4.000")
Lamp Type	LED
Length	1.22m (4.0')
Material - Guard	Butyrate
Mounting Style	Straps
Net Weight	6075.980/g
Outlet	None
Packaging Type	Carton
Socket Construction	Rubber Molded

This document was generated on Sep 11, 2025