

Specification Sheet

Part Number: LKCRF19C2



The low-profile rivet mount is designed to secure wiring bundles and fastens with the drive rivet through a predrilled hole

This mount is ideal for use in applications where space is limited

Article Number	151-27000
Type	LKCRF1
Color	Natural (NA)
Quantity Per	pack
Product Description	Low Profile Rivet Mount, 0.938" x .47", 0.25" Hole, Max Pan .134", T18-T50 Ties, 100/pkg
Short Description	Low Profile Rivet Mount, 0.938" x .47", 0.25" Hole, Max Pan .134", T18-T50 Ties, 100/pkg
Global Part Name	LKCRF1-PA66-NA

Length L (Imperial)	0.938
Length L (Metric)	24.0
Fixation Method	with Rivet (Mounts)
Width W (Imperial)	0.47
Width W (Metric)	12.0
Cable Ties	T18 - T50
Height H (Imperial)	0.157
Height H (Metric)	3.99
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.8
Panel Thickness Max (Imperial)	0.134
Panel Thickness Max (Metric)	3.40
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.4 mm
Mounting Hole Diameter D Max (Imperial)	0.255
Mounting Hole Diameter D Max (Metric)	6.4

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)
[RoHS/WEEE Compliance](#)
[Disclaimer](#)
[Terms and Conditions](#)