

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 63A IEC309 620cm

PDM3563IEC-620

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
--------------	--

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	230 V 400 V 3 phases
Provided equipment	Installation guide

Physical

Colour	Grey
Height	15.2 cm
Width	26.7 cm
Depth	30.5 cm
Net weight	20.45 kg

Input

Network frequency	50 Hz
Max line current	63 A

Output

Max current draw	63 A
Number of power socket outlets	1 IEC 309

Conformance

Product certifications	CE VDE
------------------------	-----------

Environmental

Ambient air temperature for operation	0...30 °C
Relative humidity	0...95 %

Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...4572.00 m

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	22.9 cm
Package 1 Width	50.8 cm
Package 1 Length	50.8 cm
Package 1 Weight	22.27 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)