
Specification Sheet

Part Number: FC1.2K2



Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable.

Releasable for easy access to cables when necessary.

Flat Ribbon Clamp, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Article Number	154-00011
Type	FC1.2
Color	Gray (GY)
Quantity Per	pack
Product Description	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.
Short Description	Flat Ribbon Clamp, 1.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 50/pkg

Downloaded from Arrow.com.

Global Part Name	FC1.2-PA66-GY
Length L (Imperial)	1.5
Length L (Metric)	38.1
Width W (Imperial)	2.5
Width W (Metric)	63.5
Height H (Imperial)	0.51
Height H (Metric)	12.95
Mounting Hole Diameter D (Imperial)	0.156 "
Mounting Hole Diameter D (Metric)	4.0 mm
Mounting Hole Diameter D Max (Metric)	4.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Downloaded from Arrow.com.

Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.