

[Find by Feature](#)
[Browse by Category](#)
[Share](#)
 [Search →](#)

Enter part number or keyword

[Search Results \(0\)](#)
[Search Options](#)

Select a product type to narrow your search:

Terminal ▼

Results with your selections: --

Blade size [mm] ▼

Terminal family ▼

Material ▼

Plating ▼

Gender ▼

Sealed ▼

Inside Ring Diameter [mm] ▼

Outside Ring Diameter [mm] ▼

Minimum Cable Core Cross Section [mm²] ▼

Maximum Cable Core Cross Section [mm²] ▼

Minimum Cable Diameter [mm] ▼

Maximum Cable Diameter [mm] ▼

[Clear](#)
[Search →](#)

Male Micro-Pack 100 Tin Plated Terminal, Cable Range 0.80 - 0.50 mm²

Part #12084449



[Question about this product?](#)

[Attributes](#)
[Documents \(9\)](#)

Part #:	12084449
Description:	Male Micro-Pack 100 Tin Plated Terminal, Cable Range 0.80 - 0.50 mm ²
Product Type:	Terminal
Status:	Active
Blade size [mm]:	1.0
Terminal family:	Micro-Pack
Series:	100
Gender:	Male
Sealed:	Unsealed
Material:	Tin Brass
Plating:	Tin
Minimum Cable Core Cross Section [mm²]:	0.50
Maximum Cable Core Cross Section [mm²]:	0.80
Current range [A]:	5
Temperature range [°C]:	-40 to 85
Weight [g]:	0.41
ELV compliant:	Yes

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.