

BPDH000404181O0M00

Search by : Part Number Characteristics Cross reference



MP


Closed Magnetic Circuit Type

Series Pdf

Product detail	
L(mm) ±	3.8±0.2
W(mm) ±	3.8±0.2
T(mm) ±	1.8Max.
Inductance(uH)	10
Tolerance(±%)	20
Test Frequency	100kHz,0.25V
RDC(Ω)Max	0.23
Isat(A)Max	0.84
Irms(A)Typ	1
Operating Temperature	－40℃～125℃ (Including self - temperature rise)

Part Numbering Dimensions Packing Recommended Pattern Electrical Characteristics

Downloaded from Arrow.com.



Products

Power Inductor

EMI-Common Mode Choke

EMI-Bead

RF-Signal Inductor

RF-Passives/Antennas

LAN Transformer

Resistor & Current Sensor

Applications

Automotive

Industrial

Server/DataCenter

Communication

Mobile and Tablet

Computer/Laptop

Consumer

Design Tools

Simulation Tool

Product Search Engine

E-Catalogue

About Us

Corporate Overview

Corporate Milestones

Core Technology

Certificates & Awards

Quality and Social Responsibility

Investor

Financial Information

Corporate governance

Stakeholder Contacts

Downloaded from Arrow.com.

Media Center
New Products
Events
Product Notices

Contact Us

Contact Info
Contact Form
Join Chilisin

Terms of Use
Privacy policy
Sitemap



Inductor

Resistor

Powder

Copyrights © 2018. Chilisin. All rights reserved.

Downloaded from Arrow.com.