Data Sheet | Item Number: 249-246

WCB marker tag; MARKED; 6. (20x); not stretchable; Horizontal marking; snap-on type; white

https://www.wago.com/249-246



Color: white

Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	6.
Marking (number)	20
Marking direction	Horizontal marking
Marking color	black
Marking type	Numbers
Delivery form	Marker card
Flammability class per UL94	V2

Physical data	
Height	3.6 mm / 0.142 inches
Width	2.6 mm / 0.102 inches
Depth	118.2 mm / 4.654 inches

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
Halogen-free	Yes
Weight	0.5 g
Fire load	0.014 MJ

Downloaded from Arrow.com.

Environmental requirements

Ambient temperature (storage)	-40 … +60 °C
Ambient temperature (operation)	-60 … +105 °C
Relative humidity	20 … 95 %

Commercial data

Product Group	2 (Terminal Block Accessories)
PU (SPU)	300 (10) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332276023
Customs tariff number	49119900000

Product Classification

UNSPSC	55121731
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 249-246

Downloaded from Arrow.com.