



Fixed Inductor - 1.5uH, 9.1A, 15.8mOhm

COM-16289 ROHS ✓

DESCRIPTION

FEATURES

DOCUMENTS

- Shielded
- Inductance: 1.5uH
- Tolerance: 20%
- Maximum DC Current: 9.1A
- Maximum DC Resistance: 15.8mOhms
- Minimum Operating Temperature: -40C
- Maximum Operating Temperature: +125C
- Mounting Style: PCB Mount
- Core Material: Composite

Tags

INDUCTOR

© images are [CC BY 2.0](#)



COMMENTS

0

REVIEWS

0

Comments

⚙ Looking for answers to technical questions?

We welcome your comments and suggestions below. However, if you are looking for solutions to technical questions please see our [Technical Assistance](#) page.

[Log in](#) or [register](#) to post comments.



STAY IN TOUCH WITH US

Email address

SUBMIT

Weekly product releases, special offers, and more.





ABOUT SPARKFUN

[Read Our Story](#)

[Press & Media](#)

[SparkFun Education](#) 

[Job Openings](#)

PARTNER WITH US

[See Our Partners](#)

[Become a Distributor/Reseller](#)

[Receive Volume Discounts](#)

[Build a Custom Kit](#)

[Apply for a Hardware Donation](#)

SUPPORT

[Customer Support](#)

[Purchase Orders & Payment](#)

[Terms](#)

[Technical Assistance](#)

[FAQs](#)

[Contact Us](#)

SITE INFORMATION

[Terms of Service](#)

[Privacy Policy](#)

[Compliance](#)

[Site Map](#)

SparkFun Electronics ® / **6333 Dry Creek Parkway, Niwot, Colorado 80503**

Questions? Feedback? powered by [Olark live chat software](#)