



Part Number : [1202480007](#)
Product Description : MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 4 Ports, LED for NPN Sensor, WSOR Cable, 5.0m Length
Series Number : 120248
Status : Active
Product Category : Passive Distribution Boxes
Engineering Number : BTB400N-FBW-05



Documents & Resources

Drawings
[Drawing 1202480007_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Passive Distribution Boxes
Series	120248
Description	MPIS Micro-Change (M12) Passive Junction Box, Top-Mount, 4 Ports, LED for NPN Sensor, WSOR Cable, 5.0m Length
IP Rating	IP67
Product Family	Brad Passive-Signal and Safety MPIS Boxes
Product Name	MPIS
UPC	889056329590

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A per module, 4.0A per port
Functional Wiring	NPN
Voltage - Maximum	10-30V DC
Wiring Configuration	Single I/O per Port

Physical

Bus I/O	N/A
Cable Connector Orientation	Straight
Cable Length	5.0m
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	A-Coded
LED Indicator	NPN Sensors

Material - Cable Jacket	TPU
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	628.300/g
Orientation	Top-Mount
Poles	4
Poles (wired)	4
Ports	4
Temperature Range - Operating	-25°C to +85°C
Wire/Cable Type	WSOR

This document was generated on Sep 21, 2024