Part Number : 1300190018
Product Description : Die Block 4 Pole Angle Receptacle, Orange
Series Number : 130019
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 43301



Documents and Resources

Drawings

1300190018_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130019
Description	Die Block 4 Pole Angle Receptacle, Orange
IP Rating	N/A
Product Name	Die Block
Type	Die Block
UPC	78678843301

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC

Physical

Coupling Type	Push to Lock
Gender	Female
Keyway	None
Length	N/A
Material - Component	Nitrile/PVC
Mounting Thread Size	N/A
Net Weight	194.137/g
Orientation	N/A
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	N/A

Downloaded from Arrow.com.

Wire Size (AWG)	N/A

This document was generated on Sep 26, 2026

Downloaded from Arrow.com.